



CHIP CARRIER SOCKETS:

SMPX Series

Surface Mount PLCC Socket

Product Features

Applications Include All Electronic PC Boards Requiring Use of a Socket with Same Footprints as Most Common Plastic Leaded Chip Carriers

Accepts Molded Plastic Chip Carriers Conforming to JEDEC Specification MO-047 for Square and MO-052 for Rectangular Configuration

Visual and Mechanical Polarization for PXLCC Insertion
Open Frame Design for Ease of Contact Inspection & Repair
For High Temperature SMT Soldering up to 230 °C

Optional PCB Polarizing Pegs Available
Low profile; Less than .2" Mated Height
Extraction Tool Slots*

Open Top Design for Cooler Running Chip Carrier
Automatic Insertion Machine Compatible
CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Body

High Temperature Thermoplastic, Black Color

Contact Material

Phosphor Bronze

Contact Finish

160µ" Tin over Nickel Plating

Electrical Characteristics

Contact Current Rating

1 A

Contact Resistance

15 milliohms Max.

Dielectric Withstanding Voltage

1000VAC Min. for 1 Minute

Insulation Resistance

10000 Megohms Min

Temperature Rating

-50°C to +105°C

* PXLCC Extraction Tool P/N TLPX-PXLCC

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Number of Contact	Body Type	Polarized	Packaging

Series

SMPX - Surface Mount PLCC Socket

Number of Contacts

20 - 20 Contacts

28 - 28 Contacts

32 - 32 Contacts

44 - 44 Contacts

52 - 52 Contacts

68 - 68 Contacts

84 - 84 Contacts

Polarized

N - Non-Polarized

P - Polarized

Packaging


Blank - Tubes

TR - Tape and Reel (Available only with N Option)

Contact Kycon for other Options

SMPX- Series

Dimensions in mm



Dimensions in mm

Number of Contacts	A±0.2	B±0.2	C±0.1	D±0.1	E±0.2	F±0.2	G±0.15	H±0.15
20	15.65	15.65	5.08	5.08	16.80	12.70	9.56	9.56
28	18.18	18.18	7.62	7.62	20.40	15.24	12.10	12.10
32	18.18	20.75	7.62	10.16	22.20	17.78	14.64	12.10
44	23.28	23.28	12.70	12.70	31.20	20.32	17.18	17.18
52	25.84	25.84	15.24	15.24	32.20	22.86	19.72	19.72
68	30.95	30.95	20.32	20.32	38.40	27.94	24.80	24.80
84	36.00	36.00	25.40	25.40	45.60	33.02	29.88	29.88

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[SMPX-20LCC-N](#) [SMPX-44LCC-N](#) [SMPX-32LCC-N](#) [SMPX-52LCC-N](#) [SMPX-84LCC-N](#) [SMPX-52LCC-N-TR](#) [SMPX-32LCC-N-TR](#) [SMPX-68LCC-N](#) [SMPX-28LCC-N](#) [SMPX-44LCC-N-TR](#) [SMPX-20LCC-N-TR](#) [SMPX-28LCC-N-TR](#) [SMPX-68LCC-P](#) [SMPX-52LCC-P](#) [SMPX-84LCC-P](#) [SMPX-20LCC-P](#) [SMPX-44LCC-P](#) [SMPX-32LCC-P](#) [SMPX-28LCC-P](#)