

Cat5e 350MHz Outdoor-Rated Molded Patch Cable (RJ45 M/M) - Gray, 25-ft.

MODEL NUMBER: **N007-025-GY**



Description

Tripp Lite's line of Outdoor Rated Cat5e patch cables are manufactured with high quality UV (Ultra Violet) resistant PVC cable. With an Operating Temperature range of -40C to +60C (-40F to +140F), this 25ft cable handles a wide range of weather conditions, most importantly, the degrading effects of Ultra Violet rays. Molded, snagless connectors provide a secure connection every time. Cables meet EIA/TIA 568-B.2, and are UL verified to Category 5e.

Features

- UV (Ultra Violet) Resistant Gray PVC jacket
- CMR, CMX, and UL444 Rated
- EIA/TIA 568-B.2 Compliant
- UL Verified Category 5e
- Molded, Snagless Connectors
- 4pr, Solid Conductors for long distance signal integrity

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Intended Application	Computer Networking
Cable Type	CAT5/CAT5E
Model Type	Molded

Highlights

- High Quality Outdoor Rated PVC Jacket
- Molded, Snagless RJ45 Connector

Package Includes

- 25ft Outdoor Rated Cat5e Patch Cable

INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.62
UPC ASSIGNMENT	
Unit Carton UPC#	037332125668
PHYSICAL	
Color	Gray
Style	Cat5/5e
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.