

507 SERIES CARTRIDGES FOR USE WITH HOLDERS & CLIPS

PART NO.*	COLOR	V _F	mA	CP	LIFE HOURS	FIG
507-3911-1431-600	RED	10	40	0.08	10,000	1
507-3911-1432-600	GREEN	10	40	0.08	10,000	1
507-3911-1433-600	AMBER	10	40	0.08	10,000	1
507-3911-1435-600	WHITE	10	40	0.08	10,000	1
507-3914-1471-600	RED	14	80	0.30	15,000	1
507-3914-1472-600	GREEN	14	80	0.30	15,000	1
507-3914-1473-600	AMBER	14	80	0.30	15,000	1
507-3914-1475-600	WHITE	14	80	0.30	15,000	1
507-3917-1471-600	RED	28	40	0.34	4,000	1
507-3917-1472-600	GREEN	28	40	0.34	4,000	1
507-3917-1473-600	AMBER	28	40	0.34	4,000	1
507-3917-1475-600	WHITE	28	40	0.34	4,000	1
507-3918-1437-600	CLEAR	28	40	0.30	7,000	1
507-3918-1471-600	RED	28	40	0.30	7,000	1
507-3918-1472-600	GREEN	28	40	0.30	7,000	1
507-3918-1473-600	AMBER	28	40	0.30	7,000	1
507-3918-1475-600	WHITE	28	40	0.30	7,000	1
507-5820-0747-600†	CLEAR	12	170	2.10	5,000	3
507-5821-0747-600†	CLEAR	28	40	1.20	5,000	3
507-5822-0747-600†	CLEAR	48	53	1.50	5,000	3
507-5824-0747-600†	CLEAR	120	25	1.50	5,000	3

† Use Holder 250-8758-33-504 and 250 Series Cap



Fig. 1



Fig. 2




Fig. 3

*PART NUMBER ORDERING CODE

507 - 39xx - xxxx - 600


Series

Lens Shape:


14 - Fig 1 = Cylindrical

09 - Fig 2 = Stovepipe


250 & 508 SERIES HOLDERS FOR 3/8" MOUNTING HOLE



250-8738-14-504



508-8738-504



250-8758-33-504
for Figure 3 Only

250 Series Caps for use with 507 cartridges.

CAP PART NO.	COLOR	FIG
250-3531-500	RED	4
250-3532-500	GREEN	4
250-3533-500	AMBER	4
250-3535-500	WHITE	4
250-3537-500	CLEAR	4




Fig. 4

*PART NUMBER ORDERING CODE

250 - xx38 - 14 - 504

508 - xx38 - 504

Series

Terminal Type:





87 = Turret Terminals

74 = Solder Blade (Not Shown)

75 = Solder Cups (Not Shown)

Material & Finish: Holder – Black Anodized Aluminum, Cap – Polycarbonate, Cartridge Clear Anodized Aluminum

515 SERIES CONNECTORS & SPEED CLIPS FOR 9/32" MOUNTING HOLE



Dimensions in mm [inches]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[250-8758-33-504](#) [250-7538-14-504](#) [250-3537-500](#) [250-3532-500](#) [250-3535-500](#) [250-3533-500](#) [250-8738-14-504](#)
[250-3531-500](#) [250-7438-14-504](#) [507-3911-1471-600F](#) [507-3944-0971-600F](#) [507-3914-0973-600F](#) [507-3909-0935-600F](#) [507-3911-1435-600F](#) [507-3916-1472-600F](#) [507-3904-1432-600F](#) [507-3909-0972-600F](#) [507-3916-1475-600F](#)
[507-3909-0975-600F](#) [507-3914-1476-600F](#) [507-3914-1433-600F](#) [507-3913-1471-600F](#) [507-3917-0937-600F](#) [507-3914-0937-600F](#) [507-3917-1434-600F](#) [507-3913-1475-600F](#) [507-3906-1473-600F](#) [507-3913-0975-600F](#) [507-3909-0973-600F](#) [507-3916-1473-600F](#) [507-3910-1432-500F](#) [507-3911-1433-600F](#) [507-3909-0932-600F](#) [507-3910-1433-600F](#) [507-3913-1475-600](#) [507-3905-1471-600F](#) [507-3914-0971-600F](#) [507-3911-1432-600F](#) [507-3917-0976-600F](#) [507-3913-1472-600F](#) [507-3906-1474-600F](#) [507-3918-0974-600F](#) [507-3910-1434-600F](#) [507-3909-1476-600F](#) [507-3904-1437-600F](#) [507-3914-0975-600F](#) [507-3903-1471-600F](#) [507-3917-0935-600F](#) [507-3904-1433-600F](#) [507-3944-1431-600F](#) [507-3906-1437-600F](#) [507-3917-0933-600F](#) [507-3918-1432-500F](#) [507-3917-0972-600F](#) [507-3910-1437-600F](#) [507-3918-1431-500F](#) [507-3913-0971-600F](#) [507-3917-1476-600F](#) [507-3913-1433-600F](#) [507-3910-1431-600F](#) [507-3911-1431-600F](#) [507-3911-1431-600](#) [507-3904-1431-600F](#) [507-3905-1473-600F](#) [507-3913-1476-600F](#) [507-3905-1475-600F](#) [507-3913-1435-600F](#) [507-3914-0972-600F](#) [507-3916-1471-600F](#) [507-3909-1474-600F](#) [507-3944-1471-600F](#) [507-3914-1435-600F](#) [507-3904-1434-600F](#) [507-3903-1472-600F](#) [507-3944-1472-600F](#) [507-3918-1431-600F](#) [507-3914-0931-600F](#) [507-3913-1434-600F](#) [507-3909-1473-600F](#) [507-3910-1432-600F](#) [507-3911-1435-600](#)