



Current refinements (click to remove)

[Search Tips](#)

[Region](#) [USA](#) [Product Family](#) [HSTT Heat Shrink 4 ft. Pieces and Reels](#) [Text Search: 'HSTT12-48-Q4'](#)

Your search criteria matched only one product, shown below.



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT0548-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

|                                         |                                                      |
|-----------------------------------------|------------------------------------------------------|
| Part Number:                            | HSTT1248-Q4                                          |
| RoHS Compliancy Status:                 | Compliant                                            |
| Part Description:                       | Thin Wall Polyolefin Heat Shrink                     |
| Material:                               | Flame retardant polyolefin cross-linked except clear |
| Color:                                  | Yellow                                               |
| CSA Certified:                          | Yes                                                  |
| Military Specification:                 | AMS-DTL-23053/5 Class 1                              |
| UL Recognized:                          | E122770                                              |
| Length (ft.):                           | 4                                                    |
| Length (m):                             | 1.2                                                  |
| Flammability Rating:                    | Flame Retardant                                      |
| Max. Recovered I.D. (In.):              | .062                                                 |
| Max. Recovered I.D. (mm):               | 1.6                                                  |
| Min. Expanded I.D. (In.):               | .125                                                 |
| Min. Expanded I.D. (mm):                | 3.2                                                  |
| Nominal Diameter / Size:                | .125                                                 |
| Nominal Recovered Wall Thickness (In.): | .020                                                 |
| Nominal Recovered Wall Thickness (mm):  | .5                                                   |
| Shrink Ratio:                           | 2:1                                                  |
| Temperature Range:                      | -67°F to 275°F (-55°C to 135°C)                      |
| Min. Order UOM:                         | PC                                                   |
| Min. Order Qty.:                        | 25                                                   |
| BOM Qty. (# of Pkgs.)                   | <input type="text" value="0"/>                       |

Add to My Catalog



Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.