

PART
NAME

PLASTIBOX (STYLE A)

PART
No.

PS-11301


MATERIAL: HIGH-IMPACT ABS
 COLOR: BLACK OR GRAY
 FINISH: TEXTURED BODY WITH
 SMOOTH TOP INSERT

FOUR (4) #4 x 0.250" LG. SCREWS
 SUPPLIED FOR ASSEMBLING TOP.


FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED.

*-USABLE AREA ON COVER ALSO
 AVAILABLE FOR CUSTOM MOLDING.

NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
 UNLESS OTHERWISE SPECIFIED.



0.015 RECESS
 5° TYP.
 0.260 DIA. BOSS WITH 0.093 DIA.
 HOLE x 0.310 DEEP (4) PLACES
 MOUNTING BOSSES USE EITHER M2.5 METRIC
 OR #4 STD. SHEET METAL SCREWS
 x 0.250" LG. (NOT SUPPLIED)

PART
NAME

PLASTIBOX (STYLE A)

PART
No.


PT-11308

MATERIAL: HIGH-IMPACT ABS
 COLOR: BLACK OR GRAY
 FINISH: TEXTURED BODY
 WITH TEXTURED TOP

FOUR (4) #4 x 0.375" LG. SCREWS
 SUPPLIED FOR ASSEMBLING TOP.

FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED.

NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
 UNLESS OTHERWISE SPECIFIED.



0.060 REF.
 5° TYP.
 0.260 DIA. BOSS WITH 0.093 DIA.
 HOLE x 0.310 DEEP (8) PLACES
 MOUNTING BOSSES USE EITHER M2.5 METRIC
 OR #4 STD. SHEET METAL SCREWS
 x 0.250" LG. (NOT SUPPLIED)

