


LCR CAPACITORS

LOW LOSS
POLYSTYRENE
CAPACITORS
TYPE : FSC / EX

LEADS - HEAVILY TINNED
COPPER WIRE- 0.6 MM



N.B. support must be given at the ends of the resin before preforming

CAPACITANCE	L = mm	D = mm	WORKING VOLTAGE	
				@ 50Hz
47p - 200p	12.5	5.00	630V DC	250V AC
201p - 360p	12.9	5.00	630V DC	250V AC
361p - 560p	12.9	4.50	630V DC	250V AC
561p - 680p	12.9	5.00	630V DC	250V AC
681p - 750p	12.9	5.00	630V DC	250V AC
751p - 820p	12.9	4.50	250V DC	125V AC
821p - 910p	12.9	4.50	250V DC	125V AC
911p - 1 n	12.9	4.50	250V DC	125V AC
1n1 - 1n6	12.5	5.00	160V DC	80V AC
1n61 - 2n7	12.5	4.75	160V DC	80V AC
2n71 - 3n9	12.9	5.00	160V DC	80V AC
3n91 - 6n2	17.0	5.00	160V DC	80V AC
6n21 - 7n5	17.0	5.50	160V DC	80V AC
7n51 - 8n2	17.0	6.00	160V DC	80V AC
8n21 - 10n	17.0	5.00	160V DC	80V AC
10n1 - 15n	17.0	5.50	63V DC	40V AC
15n1 - 18n	17.0	6.00	63V DC	40V AC
18n1 - 24n	17.0	6.50	63V DC	40V AC
24n1 - 30n	17.0	7.00	63V DC	40V AC
30n1 - 36n	17.0	7.50	63V DC	40V AC
36n1 - 39n	17.0	8.00	63V DC	40V AC
39n1 - 51n	17.0	10.00	63V DC	40V AC
51n1 - 68n	22.0	8.50	63V DC	40V AC
68n1 - 82n	22.0	9.50	63V DC	40V AC
82n1 - 100n	22.0	10.00	63V DC	40V AC

CAPACITANCE RANGE	47 pf - 100 nf
CAPACITANCE TOLERANCE	± 1%, ±2%, ±5%, ±10% (MIN 1.5 pf)
WORKING VOLTAGE	SEE TABLE
TEST VOLTAGE	2 X WORKING VOLTAGE
POWER FACTOR	≤0.0005 @ 1KHz ALL VALUES ≤0.0007 @ 100KHz ALL VALUES ≤0.0010 @ 1MKHz 47pf - 1nf
INSULATION RESISTANCE	>10 ⁹ MegOhm
TEMPERATURE RANGE	-40°c / +85°c
TEMPERATURE COEFFICIENT	-110 + 80ppm/°c



ISSUE 5
JULY 2001

Design may be changed without prior notification, in line with company policy of continuous improvement

LCR CAPACITORS

UNIT 18, RASSAU INDUSTRIAL ESTATE, EBBW VALE, GWENT, NP23 5SD
TEL. 01495 307070 FAX. 01495 305965