




4		3		2		1									
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS							
© COPYRIGHT — By —		ALL RIGHTS RESERVED.		H		—		P	LTR	DESCRIPTION	DATE	DWN	APVD		
NOTES: Tolerances cable lengths: 0m to 0.5m +30mm 0.5m to 1.0m +50mm 1.0m to 3.0m +100mm < 3.0m +1.5%									A	INITIAL RELEASE	12NOV2013	GSK	BvH		
									A1	ECR-15-003371	04MAR2015	GSK	BvH		
VIEW 'A' 															
TECHNICAL DATA															
Operating voltage		max. 60 V AC/DC													
Operating current per contact		max. 4 A													
Locking of ports		Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing													
Protection		IP65 and IP67 when plugged and screwed down (EN 60529)													
CABLE															
No./diameter of wires		4 x 0.25 mm²													
Wire isolation		PP (br, wh, bl, bk) (UL/CSA)													
Outer diameter		approx. 3.0 mm													
Bend radius (moving)		10 x outer diameter													
Temperature range (fixed)		-40...+80 °C													
4 pos								0.2mtr		2273015-1		4X24AWG PANELMOUNT 0.2m WIRES		1	
								LENGTH"L"		TE PN		DESCRIPTION		ITEM	
THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN 12NOV2013 SATHISH KUMAR .G		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:				CHK 12NOV2013 B.VELDHOVEN								NAME	
		0 PLC ± -				APVD 12NOV2013 A.VAN ZANDVOORT		M8 FEMALE PANEL MLD REAR MT M8 FAST PIGT							
		1 PLC ± -				PRODUCT SPEC									
		2 PLC ± -				108-19483									
		3 PLC ± -				APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO							
		4 PLC ± -				114-32127									
MATERIAL		FINISH				WEIGHT		A300779C-2273015							
CUSTOMER DRAWING						SCALE		SHEET		REV					
						NTS		1 OF 1		A1					

1470-19 (3/11)