

181-15206

Slotted Wall Wiring Duct, 1.5" X 2", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number: 181-15206

Part Number: 181-15206

Type: SL1.5X2

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)



Base Data

Part No.	181-15206
Type	SL1.5X2
Color	Gray (GY)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	1.53"
Width (W)	38.86mm
Width (W2)	1.5" / 38.1mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	1.62" / 41.1mm
Height (H)	2.06" / 52.32mm
Mounting Hole Centers	4.00" / 101.6mm

Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	CSA / UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

Logistic and Packaging

Packaging Type	box
----------------	-----

Pkg. Qty.	30 / 9.14m
Carton Qty.	120
UPC	089306293163

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)