


- NOTES :
- FOR USE ON MINI HD APPLICATOR (LEFT - RIGHT FEED).
 - TINPLATING THICKNESS .000080 MIN - .000400 MAX. (INCH).
 - MATERIAL PH.BRONZE ACC ASTM B103 ALLOY 511.
 - REAR ROLLING MUST TOUCH TAB.
 - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI**



W IRE	CRIMP HEIGHT	CRIMP WIDTH
3.0mm?	2.16mm	.130 "F"
3.5mm?	2.27mm	.130 "F"
4.0mm?	2.38mm	.130 "F"

OBSOLETE	100017-4	PRE-TINPLATED	PH.BRONZE	216331-4
	100017-3	SILVERPLATED	PH.BRONZE	216331-3
	100017-2	TINPLATED	PH.BRONZE	216331-2
	100017-1	UNPLATED	PH.BRONZE	216331-1
	LOOSE PIECE NR.	FINISH	MATERIAL	PARTNUMBER
DIRECTION OFF TOP OF REEL 107 - 3 FIG 6.	CUSTOMER DRAWING		TYCO ELECTRONICS AMP ESPAÑOLA S.A BARCELONA ESPAÑA	
	FOR REFERENCE ONLY WILL NOT BE UPDATED		THIS DRAWING IS UNPUBLISHED CUSTOMER DRAWING - -	
	© COPYRIGHT 2002 - BY AMP-ESPAÑOLA ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.			
	DR. R.v.Lokven	DATE 24.04.89	WIRE RANGE +2.5-4.0mm?	NAME .250 L.I.F AUTOMOTIVE POS LOCK REC MKII.
CHK. R.v.Lokven		DATE 24.04.89	INSUL.RANGE 3.0-4.2 DIA	REV.DATE D M Y 261109
APP. L.v.Soest	DATE 26-11-89	SIZE A2	SHEET 1 OF 1	DWG. No. C-216331 REV.LTR. L1

