


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-307IF	S-8	BA15s	28V 0.670A	C-2V

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28.0V	.603	.670	.737	—	Not Rated	—	300 Hrs

Dimensional Characteristics:

1. Base = Nickel-plated Brass Construction
2. Frosted Envelope



Title:

**S-8 Frosted Single Contact Bayonet Base Lamp
28V .670A Gas-Filled**

Drawn	06/29/09	CI	Notes: Unless otherwise specified, all dimensions are in inches.	Rev: 1
Checked	06/29/09	EB		
Approved	06/30/09	EB		