

Bearing type: ◎=Ball "B" ※=Sleeve "S" ○=1B1S "B(S)" ●=Hypro bearing "X"

PHOTO	Frame size (mm)	Model No.	Bearing Type				Rated Volt/Freq (v)	Current (A)	Power (W)	Speed (rpm)	Maximum AirFlow		Maximum Pressure		Noise (dB/A)	Weight (g)
			B	S	B(S)	X					(CMM)	(CFM)	(InAq)	(mmAq)		
	120x120x38.5	AA1281DB-AT	◎	※		●	115/50	0.12	8.24	2300	2.117	74.7	0.139	3.478	39.2	550
							115/60	0.11	7.89	1650	1.481	52.3	0.057	1.426	30.5	
		AA1281HB-AT	◎	※		●	115/50	0.25	16.30	2600	2.446	86.3	0.261	6.534	42.2	
							115/60	0.20	14.20	2900	2.721	96.1	0.231	5.779	44.5	
		AA1281LB-AT	◎	※		●	115/50	0.14	9.21	2400	2.142	75.6	0.170	4.273	40.1	
							115/60	0.13	8.86	2100	1.887	66.6	0.083	2.088	37.9	
		AA1281MB-AT	◎	※		●	115/50	0.25	15.80	2500	2.268	80.0	0.211	5.280	40.0	
							115/60	0.21	13.70	2700	2.450	86.5	0.169	4.238	41.0	
		AA1282DB-AT	◎	※		●	230/50	0.06	8.00	2300	2.117	74.7	0.139	3.478	39.2	
							230/60	0.06	7.60	1650	1.481	52.3	0.057	1.426	30.5	
		AA1282HB-AT	◎	※		●	230/50	0.12	16.00	2600	2.446	86.3	0.261	6.534	42.2	
							230/60	0.10	14.00	2900	2.721	96.1	0.231	5.779	44.5	
		AA1282LB-AT	◎	※		●	230/50	0.07	9.90	2400	2.142	75.6	0.170	4.273	40.1	
							230/60	0.07	9.40	2100	1.887	66.6	0.083	2.088	37.9	
		AA1282MB-AT	◎	※		●	230/50	0.10	13.70	2500	2.268	80.0	0.211	5.280	40.0	
							230/60	0.09	12.60	2700	2.450	86.5	0.169	4.238	41.0	

Specifications subject to change without notice.

Bearing type: ◎=Ball "B" ※=Sleeve "S" ○=1B1S "B(S)" ●=Hypro bearing "X"

PHOTO	Frame size (mm)	Model No.	Bearing Type				Rated Volt/Freq (v)	Current (A)	Power (W)	Speed (rpm)	Maximum AirFlow		Maximum Pressure		Noise (dB/A)	Weight (g)
			B	S	B(S)	X					(CMM)	(CFM)	(InAq)	(mmAq)		
	120x120x38.5	AA1282HB-AT(A1)◎	※			●	230/50	0.12	16.0	2700	2.606	91.21	0.315	8.001	42.6	550
							230/60	0.10	14.0	3100	2.923	102.51	0.380	9.652	47.0	

Specifications subject to change without notice.



◎ AA 8025



◎ AA 8038



◎ AA 9225



◎ AA 12025



◎ AA 12038



◎ AA 175