

SUNON KDE Series

DC Brushless Fan

6010**:60x60x10mm**

Model	P/N	Bearing ● VAPO ◎ SLEEVE ○ BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KDE1206PFV1	MS.G	●	12□	0.16	1.9□	5200□	16.3□	0.13□	35□	22□
KDE1206PFV2	MS.G	●	12□	0.10	1.2□	4300□	13.8□	0.09□	34.5	22□
KDE1206PFS2-8		◎	12□	0.10□	1.2□	4200□	13.9□	0.107□	30□	22□
KDE1206PFS3-8		◎	12	0.07□	0.8□	3500□	12.0□	0.09□	26□	22
KDE1206PFB2-8		○	12□	0.10□	1.2□	4400□	14.5□	0.11□	31□	27□
KDE1206PFB3-8		○	12□	0.07□	0.8□	3700□	12.7 □	0.09□	27□	27□
KDE1206PFB1	MS.G	○	12□	0.16□	1.9□	5200□	16.3□	0.13□	36□	27□
KDE1206PFB2	MS.G	○	12□	0.10	1.2	4300	13.8	0.09	35□	27□

6015**:60x60x15mm**

Model	P/N	Bearing	(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KDE0506PHS2		◎	5	0.39□	1.9□	4000□	17.8□	0.135□	31□	45
KDE0506PHS3		◎	5	0.24□	1.2□	3300□	14.8□	0.11□	26□	45□
KDE0506PHB2		○	5	0.39□	1.9□	4200□	18.5□	0.15□	31.5□	45□
KDE0506PHB3		○	5□	0.24□	1.2□	3500□	15.2□	0.13□	26.5	45□
KDE1206PHV1	MS.G	●	12□	0.15□	1.8□	4300□	20.0□	0.18□	37.5□	39□
KDE1206PHV2	MS.G	●	12□	0.09	1.1□	3800□	17.0□	0.13□	32.5□	39□
KDE1206PHS2		◎	12□	0.16□	1.9□	4000□	17.8□	0.135□	31□	45□
KDE1206PHS3		◎	12□	0.09□	1.2□	3300□	14.8□	0.11□	26□	45□
KDE1206PHB2		○	12□	0.16□	1.9□	4200□	18.5□	0.15□	31.5□	45□
KDE1206PHB3		○	12□	0.09□	1.2□	3500□	15.2	0.13□	26.5□	45□
KDE1206PHB1	MS.G	○	12□	0.15□	1.8□	4300□	20.0□	0.18□	38.5□	39□
KDE1206PHB2	MS.G	○	12□	0.09	1.1	3800	17.0	0.13	33.5	39□

6020**:60x60x20mm**

Model	P/N	Bearing	(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KDE1206PKV1	MS	●	12□	0.15	1.8□	4300□	22.0□	0.17□	32□	52
KDE1206PKV2	MS	●	12□	0.09	1.1	3600	18.5□	0.14□	27.5□	52
KDE1206PKS1		◎	12□	0.21□	2.5□	4800□	18.2□	0.16□	34□	50
KDE1206PKS2		◎	12□	0.15□	1.8□	4200□	16.5□	0.13□	31□	50□
KDE1206PKS3		◎	12	0.09□	1.1□	3200□	13.9□	0.10□	26.7□	50□
KDE1206PKB1		○	12□	0.21□	2.5□	5000□	21.2□	0.17□	37□	50□
KDE1206PKB2		○	12□	0.15□	1.8□	4400□	19.0□	0.148□	32□	50□
KDE1206PKB3		○	12□	0.09	1.1□	3500□	16.0□	0.13□	27□	50□
KDE1206PKB1	MS	○	12	0.15	1.8□	4300□	22.0□	0.17□	32.5□	52
KDE1206PKB2	MS	○	12□	0.09□	1.1	3600	18.5□	0.14	28	52

6025**:60x60x25mm**

Model	P/N	Bearing	(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KDE0506PTS2	V	◎	5	0.33□	1.7□	3700□	18.0□	0.15□	29□	60□
KDE0506PTS3	V	◎	5	0.23□	1.2□	3100□	16.0□	0.10□	25□	60□
KDE1206PTV1	MS	●	12□	0.15□	1.8□	4500□	23.0□	0.20□	33.5□	55□
KDE1206PTV2	MS	●	12□	0.09	1.1□	3800□	19.0□	0.15	30□	55
KDE1206PTS1	V	◎	12□	0.19□	2.3□	4300□	22.5	0.20□	33.5□	60□
KDE1206PTS2	V	◎	12□	0.13□	1.6□	3700□	18.0	0.15□	29	60□
KDE1206PTS3	V	◎	12□	0.09□	1.1□	3100□	16.0□	0.10□	25□	60□
KDE1206PTB1	V	○	12□	0.19□	2.3□	4500□	23.5□	0.22□	34□	60□
KDE1206PTB2	V	○	12□	0.13□	1.6□	4000	19.0□	0.16□	31□	60□
KDE1206PTB3	V	○	12□	0.09□	1.1□	3200□	16.8□	0.11□	27	60□
KDE1206PTB1	MS.(2)	○	12	0.15□	1.8□	4500□	23.0□	0.20□	34.5□	55□
KDE1206PTB2	MS.(2)	○	12	0.09	1.1	3800□	19.0□	0.15□	31□	55□
KDE1206PTB1	MS	○	12	0.15	1.8□	4500□	23.5□	0.21□	34.5□	55□
KDE1206PTB2	MS	○	12	0.09	1.1	3800	19.3	0.15	31	55□