








Copyright FCI.






PRODUCT NO	METAL CLIP	REMARKS
10036355-002LF	2 PCS	NOTE ⑧ & ⑨
10036355-002CLF		NOTE ④, ⑧ & ⑨
10036355-002C-TRLF		NOTE ④, ⑥, ⑧ & ⑨




NOTE:
ALL OTHER DIMENSIONS, REFER TO SHEET 1.



RECOMMENDED PCB LAYOUT



PART WITH PICK-UP CAP, SEE NOTE ④

spec ref		-		dr		GL L00	2004-04-20	projection				size	A3	scale	3:1	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		GL L00	2004-04-20	ecn noS10-0228								
				chr		GL L00	2010-10-28									
				appr		JOEY NG	2010-10-28	product family					SAS	rel level-		
surface -  ISO 1302	linear	0.X	±-		titleSAS RECEPTACLE VERTICAL SMT TYPE ASSY					dwg no	10036355			rev H		
		0.XX	±0.20													
		0.XXX	±-													
angular		0°	±2°	www.fci.com		cat. no.		-	Product - Customer Drw				sheet 2 of 3			

1

2

3

4

NOTES:

1. MATERIAL :
1) HOUSING : HIGH TEMP THERMOPLASTIC,
UL 94V-0, COLOR BLACK
2) TERMINAL : COPPER ALLOY
3) HOLD DOWN : COPPER ALLOY
2. FINISH :
1) TERMINAL : 30µ" Au PLATING (CONTACT POINT) OVER 50µ" NICKEL
2) SOLDER TAIL : 100µ" MIN Sn OVER 50µ" NICKEL
3) HOLD DOWN : 100µ" MIN Sn OVER 50µ" NICKEL
- ③. PER SFF REV 1.1
- ④. PART WITH PICK-UP CAP, P/N XXXXXXXXX-XXXC LF.
- ⑤. THE STD PACKAGING IS IN TRAY
- ⑥. FOR TAPE & REEL PACKAGING, SUFFIX "-TR" ADDED
P/N: XXXXXXXXX-XXXC-TR LF
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN.
- ⑧. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ⑨. PART NUMBERS ENDING IN "LF" MEANS FOR NOTE 8 LEAD FREE IDENTIFICATION
THE EQUIVALENT P/N FOR "LF" DESIGNATION.

△H

(i) XXXXXXXXX-XXXLF IS SAME AS XXXXXXXXX-XXX



(ii) XXXXXXXXX-XXXCLF IS SAME AS XXXXXXXXX-XXXC

(iii) XXXXXXXXX XXXC TRLF IS SAME AS XXXXXXXXX XXXC TR
- △H

10. A △H SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

spec ref -				dr GL L00		2004-04-20		projection 	MM 	size A3		scale 3:1	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng GL L00		2004-04-20				ecn no S10-0228			
				chr GL L00		2010-10-28				rel level -			
				appr JOEY NG		2010-10-28		product family SAS					
surface  ISO 1302	linear	0.X ± -			title SAS RECEPTACLE VERTICAL SMT TYPE ASSY				dwg no 10036355	rev H			
		0.XX ±0.20											
		0.XXX ± -											
	angular	0° ±2°		www.fci.com	cat. no. -		Product - Customer Drw				sheet 3 of 3		

2

3

PDS: Rev :H

STATUS:Released

Printed: Nov 01, 2011