




REV. A

DCO 144374

COIL: @ 25°C

RESISTANCE 3300 OHMS ±10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.0 VDC

MUST RELEASE 8.0 VDC MAX., 1.4 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX.

RELEASE TIME 2.0 MS MAX.

CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 14AUG2007

CK. J.M.B. 8/15/07

Tyco Electronics

©COPYRIGHT 2005

TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. QPL

CUST. NO. M39016/11-023M REV.

TYCO NUMBER
ELECTRONICS
1617131-4

CII PART NUMBER

JMSW -26XM