




MATERIALS	SPECIFICATIONS
BODY: Phenolic, UL94 V-0	FUNCTION: 1P1T OFF-(ON)
ACTUATOR: Nickel Plated Brass	RATINGS: ANSI/UL1054 and CAN/CSA C22.2 No.55 (E194579): 20A 125VAC [cURus] 15A 277VAC [cURus] 1.5HP 125/277VAC [cURus]
BUSHING: Nickel Plated Brass	CONTACT RESISTANCE: Initial: 50mΩ Max. at 50VAC
HOUSING: Stainless Steel	INSULATION RESISTNACE: 800MΩ Min. at 500VDC
HARDWARE: Nickel Plated Steel	DIELECTRIC STRENGTH: 1,500VAC for 1 Minute
FUNCTION PLATE: Stainless Steel	OPERATING LIFE: 6,000 Cycles [cURus]
SPACER PLATE: Laminate Board	TEMPERATURE: Operating: -20°C to 85°C [cURus]
SPRING: Steel	APPROVALS:  RoHS COMPLIANT
PLUNGER: Nylon	
MOBILE CONTACT: Silver Plated Copper	
MOBILE CONTACT PIVOT: Silver Plated Copper	
CONTACTS: Silver Alloy Clad Copper	
TERMINALS: Brass Steel	