



A

クレモン

ローラー
締り

特装密閉
ハンドル

フリーザー
密閉

平面
スイング

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L 型
ハンドル

T 型
ハンドル

丸型
小型

押ボタン

取手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ

A-2176・A-1176・A-176 つまみ

足長ローレットつまみ LONG SHANK KNURLED KNOB FASTENERS

PAT.PEND.


A-2176 チタン製 A-1176 ステンレス製 A-176 黄銅製



- 仕様 ●材質: A-2176/純チタン2種
A-1176/ステンレス鋼(SUS303)
A-176/快削黄銅棒(C3602BD)
- 表面仕上: A-2176・A-1176/鏡面バフ研磨
A-176/クロムめっき(MBCr)
- 付属品: ナイロンワッシャー1枚(追加のナイロンワッシャーは別売りです。)
- 用途 ●配分電盤・制御機器・自動販売機
- 納期 ●標準在庫品(チタン製はお問合せください)
- 備考 ●表の寸法以外も製作致します。
●SUS304・SUS316も製作致します。お問合せください。

- Specifications ●Material: A-2176: Pure titanium grade 2
A-1176: Stainless steel (SUS303)
A-176: Free cutting brass (C3602BD)
- Finish: A-2176・A-1176: Mirror surface buffing
A-176: Chrome plating (MBCr)
- Accessories: One nylon washer.
(Additional nylon washers are available separately.)
- Specific-use ●Power/distribution boards, control equipment and vending machines


[A-2176・A-1176-11~32・A-176-11~32]



抜け止めワッシャー
CP-29-PAが使用できます
(1348ページ参照)



[A-1176-40~50・A-176-40~50]



商品番号 Product No.	RoHS	CAD	材質 Material	L1	L2	L3	φD1	φD2	φD3	φD4	M	製品質量(g) Mass	コード Code	単価 Price	数量 Quantity	価格 Price
A-2176-13	●	2D/3D	チタン Ti	36	21	9	18	10	4.8		M6	11	03433			
A-2176-18	●	2D/3D	チタン Ti	22	14	8	15	8	4	10	M5	6	03434			
A-2176-22	●	2D/3D	チタン Ti	10	6	8	14	8	3		M4	4	03435			
A-1176-31	●	2D/3D	SUS	50	35							40	00930	¥530	20個~	¥504
A-1176-11	●	2D/3D	SUS	44	24	11	22	12	5.8	14	M8	38	00762	¥490	20個~	¥466
A-1176-12	●	2D/3D	SUS	34	19							36	00763	¥460	20個~	¥437
A-1176-32	●	2D/3D	SUS	50	35							24	00931	¥420	20個~	¥399
A-1176-13	●	2D/3D	SUS	36	21	9			4.8		M6	20	00764	¥380	30個~	¥361
A-1176-14	●	2D/3D	SUS	26	16							14	00765	¥310	30個~	¥295
A-1176-15	●	2D/3D	SUS	21	13							14	00766	¥300	30個~	¥285
A-1176-16	●	2D/3D	SUS	37	22							13	00767	¥300	30個~	¥285
A-1176-17	●	2D/3D	SUS	27	17							12	00768	¥280	30個~	¥266
A-1176-18	●	2D/3D	SUS	22	14							11	00769	¥270	30個~	¥257
A-1176-19	●	2D/3D	SUS	27	17	8						10	00770	¥270	30個~	¥257
A-1176-20	●	2D/3D	SUS	20	12							9	00771	¥260	30個~	¥247
A-1176-21	●	2D/3D	SUS	15	10							8	00772	¥250	30個~	¥238
A-1176-22	●	2D/3D	SUS	10	6							7	00773	¥240	30個~	¥228
A-176-31	●	2D/3D	黄銅 Brass	50	35							40	00913	¥410	20個~	¥390
A-176-11	●	2D/3D	黄銅 Brass	44	24	11	22	12	5.8	14	M8	38	00402	¥280	30個~	¥269
A-176-12	●	2D/3D	黄銅 Brass	34	19							36	00403	¥270	30個~	¥259
A-176-32	●	2D/3D	黄銅 Brass	50	35							24	00914	¥320	30個~	¥307
A-176-13	●	2D/3D	黄銅 Brass	36	21	9			4.8		M6	20	00404	¥220	30個~	¥211
A-176-14	●	2D/3D	黄銅 Brass	26	16							14	00405	¥150	50個~	¥144
A-176-15	●	2D/3D	黄銅 Brass	21	13							14	00406	¥150	50個~	¥144
A-176-16	●	2D/3D	黄銅 Brass	37	22							13	00407	¥160	40個~	¥154
A-176-17	●	2D/3D	黄銅 Brass	27	17							12	00408	¥140	50個~	¥134
A-176-18	●	2D/3D	黄銅 Brass	22	14							11	00409	¥140	50個~	¥134
A-176-19	●	2D/3D	黄銅 Brass	27	17	8						10	00410	¥130	50個~	¥125
A-176-20	●	2D/3D	黄銅 Brass	20	12							9	00411	¥120	60個~	¥115
A-176-21	●	2D/3D	黄銅 Brass	15	10							8	00412	¥110	60個~	¥106
A-176-22	●	2D/3D	黄銅 Brass	10	6							7	00413	¥110	60個~	¥106

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

商品番号 Product No.	RoHS	CAD	材質 Material	L1	L2	φD1	φD2	φD3	M	製品質量(g) Mass	コード Code	単価 Price	数量 Quantity	価格 Price
A-1176-40	●	3D	SUS	45	25		18	6	14	M8	45	01612	¥480	20個~ ¥461
A-1176-41	●	3D	SUS	35	20						43	01613	¥430	20個~ ¥413
A-1176-42	●	3D	SUS	45	25						32	01614	¥400	30個~ ¥384
A-1176-43	●	3D	SUS	35	20		16	4.8		M6	30	01615	¥380	30個~ ¥365
A-1176-44	●	3D	SUS	25	15						28	01616	¥340	30個~ ¥326
A-1176-45	●	2D/3D	SUS	35	20						26	01617	¥350	30個~ ¥336
A-1176-46	●	2D/3D	SUS	25	15	15	4.1		10	M5	24	01618	¥330	30個~ ¥317
A-1176-47	●	2D/3D	SUS	20	10						23	01619	¥280	30個~ ¥269
A-1176-48	●	2D/3D	SUS	30	15						21	01620	¥320	30個~ ¥307
A-1176-49	●	2D/3D	SUS	20	10	14	3			M4	19	01621	¥310	30個~ ¥298
A-1176-50	●	2D/3D	SUS	15	8						19	01622	¥280	30個~ ¥269
A-176-40	●	2D/3D	黄銅 Brass	45	25		18	6	14	M8	45	01598	¥260	30個~ ¥250
A-176-41	●	2D/3D	黄銅 Brass	35	20						43	01599	¥230	30個~ ¥221
A-176-42	●	2D/3D	黄銅 Brass	45	25						32	01600	¥220	30個~ ¥211
A-176-43	●	2D/3D	黄銅 Brass	35	20	16	4.8			M6	30	01601	¥200	40個~ ¥192
A-176-44	●	2D/3D	黄銅 Brass	25	15						28	01602	¥170	40個~ ¥163
A-176-45	●	2D/3D	黄銅 Brass	35	20						26	01603	¥180	40個~ ¥173
A-176-46	●	2D/3D	黄銅 Brass	25	15	15	4.1		10	M5	24	01604	¥160	40個~ ¥154
A-176-47	●	2D/3D	黄銅 Brass	20	10						23	01605	¥150	50個~ ¥144
A-176-48	●	2D/3D	黄銅 Brass	30	15						21	01606	¥160	40個~ ¥154
A-176-49	●	2D/3D	黄銅 Brass	20	10	14	3			M4	19	01607	¥140	50個~ ¥134
A-176-50	●	2D/3D	黄銅 Brass	15	8						19	01608	¥140	50個~ ¥134

※大量のご注文は更にお安くなります。