


# EIA -Based VectorPak™ Subrack Systems

## Rack Accessories



### "P" Type Side Panel


Material: 0.080" aluminum with clear irridite finish

| Part No.     | Overall Height A | Depth B | Vector Handle | Accepts Max Card Height | Rack Units (H) |
|--------------|------------------|---------|---------------|-------------------------|----------------|
| SW34P89/90   | 3.48"            | 9.0"    | HA13          | 2.75"                   | 2U             |
| SW34P119/90  | 3.48"            | 12.0"   | HA13          | 2.75"                   | 2U             |
| SW34P156/90  | 3.48"            | 15.75"  | HA13          | 2.75"                   | 2U             |
| SW52P89/90   | 5.23"            | 9.0"    | HA12          | 4.5"                    | 3U             |
| SW52P119/90  | 5.23"            | 12.0"   | HA12          | 4.5"                    | 3U             |
| SW52P156/90  | 5.23"            | 15.75"  | HA12          | 4.5"                    | 3U             |
| SW69P89/90   | 6.98"            | 9.0"    | HA13          | 6.25"                   | 4U             |
| SW69P119/90  | 6.98"            | 12.0"   | HA13          | 6.25"                   | 4U             |
| SW69P156/90  | 6.98"            | 15.75"  | HA13          | 6.25"                   | 4U             |
| SW87P89/90   | 8.73"            | 9.0"    | HA12          | 8.0"                    | 5U             |
| SW87P119/90  | 8.73"            | 12.0"   | HA12          | 8.0"                    | 5U             |
| SW87P156/90  | 8.73"            | 15.75"  | HA12          | 8.0"                    | 5U             |
| SW104P89/90  | 10.47"           | 9.0"    | HA12          | 9.75"                   | 6U             |
| SW104P119/90 | 10.47"           | 12.0"   | HA12          | 9.75"                   | 6U             |
| SW104P156/90 | 10.47"           | 15.75"  | HA12          | 9.75"                   | 6U             |
| SW122P156/90 | 12.22"           | 15.75"  | HA12          | 11.5"                   | 7U             |
| SW122P202/90 | 12.22"           | 20.25"  | HA12          | 11.5"                   | 7U             |
| SW157P119/90 | 15.72"           | 12.0"   | HA19-9U       | 15.0"                   | 9U             |

## Modules or Front Panel Mounting Hardware

SC 10-2A Thumb screws and SC10-3A jack screws (supplied with EFP modules, Cardmount modules and front assemblies to T-struts. SP09-2 spacers are used as standoffs for mounting modules to 1" T-struts (1.79" struts are standard with module subracks.)


| Part No. | Description                                                     | Pkg Qty |
|----------|-----------------------------------------------------------------|---------|
| SP09-2   | Hex spacer for module mounting, includes hardware               | 12      |
| SC10-2A  | Thumb screw fully threaded for direct attachment of panels      | 12      |
| SC10-3A  | Jack screw for mounting modules to T-struts with jacking action | 12      |



THE FOLLOWING ACCESSORIES ARE NOT COMPATIBLE WITH CCE-STYLE ENCLOSED RACKS ON THE PREVIOUS PAGE

### Top and Bottom Card Rack Covers - CAC1, CAC2, CAC3

Two 1/16" thick aluminum covers with clear irridite finish provide protection over and under the card area, is designed to snap into opposing groves in the horizontal T-Strut rails. Rear panels CRK3, CRK5, CRK7 includes attachment hardware for mounting onto Vectorpak P-type side-panels are easy to customize.



CAC1 and CRK3

### Bottom Hinged Front Panels - HFP52-1

These are designed for use as a front "drop-down" panel with lanyard for holding the panel at 90°. Provides a work surface and prevents damage to equipment. Comes complete with hardware and full instructions. Panels are 1/8" thick brushed aluminum with clear irridite finish.



CCA13S with HFP52-1

| Use With Rack Size   | Height | Width  | Depth  | Bottom Hinged Front Panels (w/L20 lanyard) | Rear Panels | Top / Bottom solid Covers | Rack Flange Dress Panels (3" wide) | Rack Handles (Sold as pair) |
|----------------------|--------|--------|--------|--------------------------------------------|-------------|---------------------------|------------------------------------|-----------------------------|
| (Actual wall height) |        |        |        |                                            |             |                           |                                    |                             |
| 3U                   | 5.23"  | 19.00" | 9.00"  | HFP52-1                                    | CRK3        | CAC1                      | FP52-2                             | HA12                        |
| 3U                   | 5.23"  | 19.00" | 12.00" | HFP52-1                                    | CRK3        | CAC2                      | FP52-2                             | HA12                        |
| 3U                   | 5.23"  | 19.00" | 15.75" | HFP52-1                                    | CRK3        | CAC3                      | FP52-2                             | HA12                        |
| 4U                   | 6.98"  | 19.00" | 12.00" | HFP69-1                                    | CRK5        | CAC2                      | FP69-2                             | HA13                        |
| 4U                   | 6.98"  | 19.00" | 15.75" | HFP69-1                                    | CRK5        | CAC3                      | FP69-2                             | HA13                        |
| 5U                   | 8.73"  | 19.00" | 12.00" | HFP87-1                                    | CRK7        | CAC2                      | FP87-2                             | HA12                        |
| 5U                   | 8.73"  | 19.00" | 15.75" | HFP87-1                                    | CRK7        | CAC3                      | FP87-2                             | HA12                        |

