



GMS 120 Professional



Advantages: GMS 120 Professional

The most reliable multi-detector in its class

- Maximum reliability: most objects are found and application errors are avoided due to the automatic calibration
- Reliable detection even of deep-lying objects – up to a depth of 12 cm
- Even more reliable detection of objects due to three-colour LED luminous ring
- Pinpoint indication of the object's centre with the Centre Finder scale, and display of material properties
- Better visibility of the result due to illuminated display
- Marking hole with LED luminous ring
- Three detection modes for various applications: Drywall mode, metal mode, live cable mode



Technical data: GMS 120 Professional

Detectable materials	Ferrous metals, non-ferrous metals, wooden substructures, live cables
Max. detection depth	120 mm
Detection depth, steel, max.	120 mm
Detection depth, copper, max.	80 mm
Detection depth of live cables, max.	50 mm
Detection depth of wooden substructures, max.	38 mm
Automatic deactivation facility, approx.	5 min
Power supply	1 x 9 V 6LR61
Weight, approx.	0,27 kg
Length	200 mm
Width	85 mm
Height	32 mm
Dust and splash guard	IP 54