

**ebm-papst Landshut GmbH**

Hofmark-Aich-Straße 25

84030 Landshut

Phone: +49 871 707-0

Fax: +49 871 707-465

www.ebmpapst.cominfo3@de.ebmpapst.com**Nominal data**


Type	QLZ06/2400-3030	
Nominal voltage	[VAC]	230
Frequency	[Hz]	50
Speed	[min ⁻¹]	1700
Power input	[W]	33
Current draw	[A]	290
Max. back pressure	[Pa]	63
Min. ambient temperature	[°C]	0
Max. ambient temperature	[°C]	60
Air flow	[m ³ /h]	170

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Technical features

Dimensions	60 mm
Connection line	Flat plug 6.3 x 0.8
Line	Standard
Mounting position	Horizontal or vertical with motor below
Insulation class	B F or H also available on request
Mass	1.40 kg


Product drawing



AC tangential blower

forward curved

Charts: Air flow



AC tangential blower

forward curved

Charts: Speed

