



General Information

Kit Part Number:	4-2110842-1
Description:	Multi-Purpose, Flame-Retardant, Flexible, Low Shrink Temperature, Polyolefin Tubing for Insulation and Strain Relief
Application:	Cable Jacketing, Color Coding, Identification, Insulation and Protection, Terminators, Wire Bundling, Wire Splices
Family:	VERSAFIT
TE Brand:	RAYCHEM Products
Solution:	Heat Shrinkable Products
Product Type:	Tubing Products
Number of Pieces:	126
RoHS:	Yes

Specifications

Adhesive Lined:	No
Color:	Black
Expanded ID:	1/2" (12.70mm), 1" (25.40mm), 1/4" (6.35mm), 3/8" (9.53mm), 3/4" (19.05mm), 3/16" (4.75mm)
Shrink Ratio:	2:1
Tool Included:	No
Voltage Rating:	600V
Wire Gauge (AWG):	2/0-4/0, 2-1/0, 6-3, 8, 12-10, 18-16, 18-14

Product Highlights

Highly Flame-Retardant, Very Flexible, Low-Shrink-Temperature, Polyolefin Tubing

Features and Benefits

- 2:1 Shrink Ratio
- Low Recovery Temperature
- Meets or Exceeds Commercial, Industrial and Military Standards

Applications

- Wire Splices
- Terminators
- Cable Jacketing
- Color Coding
- Identification
- Insulation and Protection
- Wire Bundling



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
D76139-000	30	VERSAFIT Heat Shrink Tube 3/16" ID, 6" Length	Datasheet	Details	Search
F37063-000	28	VERSAFIT Heat Shrink Tube 1/4" ID, 6" Length	Datasheet	Details	Search
D27573-000	24	VERSAFIT Heat Shrink Tube 3/8" ID, 6" Length	Datasheet	Details	Search
C02462-000	20	VERSAFIT Heat Shrink Tube 1/2" ID, 6" Length	Datasheet	Details	Search
A92664-000	14	VERSAFIT Heat Shrink Tube 3/4" ID, 6" Length	Datasheet	Details	Search
C21270-000	10	VERSAFIT Heat Shrink Tube 1" ID, 6" Length	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
----------	-----------------





