


U.S. Footprint

Number of contacts

9–37

Mounting height



Stamped solder pins, angled with snap-in-clips and grounding board locks

Identification		No. of contacts	Part No.	
D-Sub	Performance levels Explanations see page 05.04 Other performance levels on request		Performance level 3	S4 ¹⁾
	Male connector metal shell with dimples			
			2.84 mm pitch	2.84 mm pitch
		9	09 68 163 781 .	09 68 163 581 .
		15	09 68 263 781 .	09 68 263 581 .
		25	09 68 363 781 .	09 68 363 581 .
		37	09 68 463 781 .	09 68 463 581 .
	Female connector metal shell			
			2.84 mm pitch	2.84 mm pitch
		9	09 68 153 761 .	09 68 153 561 .
		15	09 68 253 761 .	09 68 253 561 .
		25	09 68 353 761 .	09 68 353 561 .
		37	09 68 453 761 .	09 68 453 561 .
	Please insert digit for flange thread or fitted female screw locks			
	M3 ▶ 1 ²⁾			
	4-40 UNC ▶ 2			
	fitted screw locks 4-40 UNC ▶ 3			

¹⁾ S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

²⁾ Not normally kept in stock