



(2,00 mm) .0787"

TCMD-20-D-02.50-01

TCMD-08-D-02.50-01-R

TCMD SERIES

HIGH RELIABILITY IDC HEADER CABLE

Mates with:
SMM*, MMS*, ESQT,
PTF, SQT, SQW, TLE

SPECIFICATIONS

For complete specifications
see www.samtec.com?TCMD

Insulator Material:
Black Glass Filled Polyester

Terminal:
Phosphor Bronze

Plating:
Au or Sn over
50µ" (1,27 µm) Ni

Wire:
28 AWG 7/36 Stranded,
Tinned, Copper with
Gray PVC Insulator

Operating Temp Range:
-40°C to +105°C

RoHS Compliant:
Yes

RECOGNITIONS

For complete scope
of recognitions see
www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other sizes
Contact Samtec.

TYPE STRIP — NO. PINS PER ROW — END OPTION — OVERALL LENGTH — 01 — TRANSFER OPTION — OTHER OPTION

—04, —05,
—06, —07,
—08, —10, —12,
—13, —15, —17,
—20, —22, —25
(Standard sizes)

—"XX.XX"
= Assembled Length


Assembled Length
in INCHES (±1/8")
2 inches minimum

Leave blank for —S and —D
End Options. For —T End
Option Specify "N"
(Socket has notch polarization)




• Strain relief option


—S = Single End




—D = Double End



—T = Transfer End



—P "XX"
= Position Polarization



Specify "XX" as position
number. Requires
Transfer End. Only
Socket is polarized. 1

—SR
= Strain Relief

No. of positions x
(2,00) .0787 + (7,874) .3100


Not available with —O, —M,
—R, —DXX or —BXX

—D "XX"
= Daisy Chain

"XX" ± 1/8"
Double
Row
Connectors
Outer
Most
(End
of
assembly) 4


—B "XX"
= Breakout

Specify "XX" as number of
conductors to be broken out.




Breakout starts with Number 1
lead indicated by brown wire or
red stripe. Shown on top side. 2


—R
= Reversed




—M
= Middle Reverse



—O
= Outside Reverse




—RW
= Reverse Wiring



Blue or black wire
opposite position #1. 3

TCMD = Terminal Strip



***Note:** Standard TCMD callout
will not mate with SMM, MMS.
Must use gold plated callouts.
(See drawing on web.)
When mated with a socket,
Wire 1 mates with Pin 2;
Wire 2 mates with Pin 1, etc.

Note: TCMD Series
assemblies are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685