

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050028](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Super-Safeway Rubber Hand Lamp 75W with LOVOLT In-line Transformer Screw Release Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130105
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Specialty Lighting
Product Name	Super-Safeway
Type	Hand Lamps, Specialty Light
UPC	78678862500

Physical

Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Screw Release
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	75W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Material Info

Engineering Number	1600-12A
--------------------	----------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130105](#) Series