

Screw plug


10xx PG

Configuration

Screw plug	Polystyrene
Connecting thread	Pg as per DIN 40430

Properties

	for secure sealing of unused threaded or clearance hole
Temperature range	-20°C +70°C
Protection grade	IP54 higher protection grade possible if assembled with sealing ring



Features



RAL 7035

A	L	H	Da		Part No.
	mm	mm	mm	Piece	
Pg 7	6	10	15	100	1007 PG
Pg 9	6	10	19	100	1009 PG
Pg 11	6	10	22	100	1011 PG
Pg 13,5	6	10	25	100	1013 PG
Pg 16	6	10	27	100	1016 PG
Pg 21	8	12,5	33	100	1021 PG
Pg 29	8	13	44,5	100	1029 PG
Pg 36	10	15	55,5	50	1036 PG
Pg 42	10	15,5	62,5	50	1042 PG
Pg 48	12	17	69,5	50	1048 PG