

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [112011-0004](#)
Status: **Active**
Overview: Brad® PC Network Interface Cards (NIC)
Description: applicom PCU1500PFB Card, Profibus (DP, S7/MPI, S5, FDL), 1 Channel, PCI 3.3/ 5V
- OPC/DLL/DAS - SCADA/HMI

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Network Interface
Series	112011
Application	HMI, SCADA
Approvals	CE certified
Communication Speed	Profibus: 9.6 kbps to 1.5 Mbps
Messaging	Profibus* DP V0 Master, Profibus* FDL S5 Client, Profibus* FDL Send/Receive, Profibus* MPI Master, Profibus* S7 Client
Mounting Style	PC Slot
Operating System	Windows 7, Windows Server 2003, Windows Server 2008, Windows Vista, Windows XP
Overview	Brad® PC Network Interface Cards (NIC)
Product Literature Order No	987650-5288
Product Name	applicom®
Protocol	Profibus*
Slot	Universal PCI 3.3V/5V
Software Downloads	APP-PFB-PCU
Type	Profibus* Card
UPC	78678894845

Physical


Channels	1
Interface	DAServer, DDE Server, DLL, OPC DA Server
Net Weight	219.570/g
Network Connection Type	Profibus* D-Sub Female (9 pin)
Packaging Type	Carton
Processor	AMD SC520
Temperature Range - Operating	0°C to +65°C

Electrical

Current - Maximum Input	5.5W
EMC	EN 61000-3-2, EN 61000-3-3, IEC 61000-6-2
Supply Voltage	3.3/5V

Material Info

Old Part Number	APP-PFB-PCU-C
-----------------	---------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[112011Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

112011-0004