



615

Single Input Manometer

Features

- Single input with +/-80" H2O range.
- Seven units of measure (mbar, kPa, PSI, mmHg, inHg, mmH2O, inH2O).
- Display - 4 digit with backlight
- Smooth - Stabilizes display when measuring fluctuating pressures
- Data Hold - Freezes reading on display.
- Min / Max - Records Min/Max readings
- Auto Off - Conserve battery power.

Specifications

- Measurement Range:** ± 80 " H2O
- Display:** 4 Digit LCD with backlight
- Input Type:** Single (1/4" Barbed)
- Resolution (max):** 0.01" H2O
- Accuracy:** +/- (0.5% of reading + 5 digits)
- Functions:** One Touch Zero, Data Hold, Back-light, Unit Selection, Smoothing, Auto power Off, Min / Max Record
- Units of Measure:** 7 Units (mbar, kPa, PSI, mmHg, inHg, mmH2O, inH2O)
- Battery Type:** 9V alkaline
- Battery Life:** 80hours (Typical)
- Auto Power Off:** 40 minutes

