



**Mod. 5833**

Exceptional resistance to impact, corrosion, water, dust, and atmospheric agents in general.

- Two man lift
- Side handles
- Locking telescopic handle
- Self-oiling free running wheels
- Body of the case made of thick plastic resin
- Neoprene seal
- Pressure valve quickly adjusts internal pressure in case of sudden changes in height or temperature
- Ergonomic handle and strong pressure locks that can be padlocked
- Interstackable (even if different-size models)
- Internal fitting for metal supports to set up panels or masks for attachment of tools and equipment



Blocking handle in use position




Activate Blocking Lever



Return to Position of Rest

|                             |   |
|-----------------------------|---|
| Panels, Bags and dividers   |   |
| Colours                     | Black<br>Orange<br>Military green   |
| Versions                    | 5833.B Black with foam<br>5833.O Orange with foam<br>5833.G Green with foam<br>5833.B E Black empty<br>5833.O E Orange empty<br>5833.G E Green empty  |
| Accessories and Spare parts | <p>Foam kit<br/>Cod. FOAM.5833</p> <p>Neoprene seal<br/>Cod. NEOSEAL27</p> <p>Identification label (with protective cover)<br/>Cod. LABELCOVER.2712</p> <p>Purge valve - (black colour)<br/>Cod. PURGEVALVE.B</p> <p>Panel support kit - Cod. KIT SUPP.EXPL. (6 pcs. + screws kit)</p> <p>Plastic Panel support kit - Cod. KIT SUPP.PLAST. (6 pcs. + screws kit and nuts)</p> <p>Patented padlock (with 2 keys)<br/>Cod. EXPL.PADLOCK</p> <p>Patented combination padlock<br/>Cod. EXPL.COMBILOCK</p> |



| Internal dimensions |          |        |        |         |
|---------------------|----------|--------|--------|---------|
| A                   | B        | C      | D      | E       |
| 580 mm              | 440 mm   | 330 mm | 60 mm  | 270 mm  |
| 22 13/16"           | 17 5/16" | 13"    | 2 3/8" | 10 5/8" |

| External dimensions - mm. |               |                |
|---------------------------|---------------|----------------|
| A                         | B             | C              |
| 682 mm                    | 510 mm        | 355 mm         |
| 26 7/8"                   | 20 1/16"      | 14"            |
| Weight - 9 kg. / 19 Lbs.  |               |                |
| Temperature rating        | -33°C / +90°C | -27°F / +194°F |