





DUAL-IN-LINE HEADERS

SERIES 150, 153 • SOLDER TAIL AND WRAPOST • OPEN FRAME



- Series 150 DIL Headers are equipped with .025" dia. pins MM #0290. See page 215 for details
- Series 153 DIL Headers have 3-level wrapposts MM #5301. See page 227 for details
- Both series have .018" dia. solder tails which are pluggable into standard contacts
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION			
	A	B	C		Solder Tail	3 Level Wrappost		
10	0.5	0.2	0.3	40	150-XX-210-00-001000	153-XX-210-00-001000		
4	0.2	0.3	0.4	102	150-XX-304-00-001000	153-XX-304-00-001000		
6	0.3	0.3	0.4	67	150-XX-306-00-001000	153-XX-306-00-001000		
8	0.4	0.3	0.4	50	150-XX-308-00-001000	153-XX-308-00-001000		
10	0.5	0.3	0.4	40	150-XX-310-00-001000	153-XX-310-00-001000		
14	0.7	0.3	0.4	29	150-XX-314-00-001000	153-XX-314-00-001000		
16	0.8	0.3	0.4	25	150-XX-316-00-001000	153-XX-316-00-001000		
18	0.9	0.3	0.4	22	150-XX-318-00-001000	153-XX-318-00-001000		
20	1.0	0.3	0.4	20	150-XX-320-00-001000	153-XX-320-00-001000		
22	1.1	0.3	0.4	18	150-XX-322-00-001000	153-XX-322-00-001000		
24	1.2	0.3	0.4	16	150-XX-324-00-001000	153-XX-324-00-001000		
28	1.4	0.3	0.4	14	150-XX-328-00-001000	153-XX-328-00-001000		
20	1.0	0.4	0.5	20	150-XX-420-00-001000	153-XX-420-00-001000		
22	1.1	0.4	0.5	18	150-XX-422-00-001000	153-XX-422-00-001000		
24	1.2	0.4	0.5	16	150-XX-424-00-001000	153-XX-424-00-001000		
28	1.4	0.4	0.5	14	150-XX-428-00-001000	153-XX-428-00-001000		
32	1.6	0.4	0.5	12	150-XX-432-00-001000	153-XX-432-00-001000		
24	1.2	0.6	0.7	16	150-XX-624-00-001000	153-XX-624-00-001000		
28	1.4	0.6	0.7	14	150-XX-628-00-001000	153-XX-628-00-001000		
32	1.6	0.6	0.7	12	150-XX-632-00-001000	153-XX-632-00-001000		
36	1.8	0.6	0.7	11	150-XX-636-00-001000	153-XX-636-00-001000		
40	2.0	0.6	0.7	10	150-XX-640-00-001000	153-XX-640-00-001000		
42	2.1	0.6	0.7	9	150-XX-642-00-001000	153-XX-642-00-001000		
48	2.4	0.6	0.7	8	150-XX-648-00-001000	153-XX-648-00-001000		
50	2.5	0.6	0.7	8	150-XX-650-00-001000	153-XX-650-00-001000		
52	2.6	0.6	0.7	7	150-XX-652-00-001000	153-XX-652-00-001000		
50	2.5	0.9	1.0	8	150-XX-950-00-001000	153-XX-950-00-001000		
52	2.6	0.9	1.0	7	150-XX-952-00-001000	153-XX-952-00-001000		
64	3.2	0.9	1.0	6	150-XX-964-00-001000	153-XX-964-00-001000		
					SPECIFY PLATING CODE XX =	10 ◆	90	40 ◆
					Pin Plating 	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn

RoHS-2
2011/65/EU

XX=Plating Code
See Below



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[153-10-964-00-001000](#) [153-10-952-00-001000](#) [153-10-950-00-001000](#) [153-10-652-00-001000](#) [153-10-650-00-001000](#) [153-10-648-00-001000](#) [153-10-642-00-001000](#) [153-10-640-00-001000](#) [153-10-636-00-001000](#) [153-10-632-00-001000](#) [153-10-628-00-001000](#) [153-10-624-00-001000](#) [153-10-432-00-001000](#) [153-10-428-00-001000](#) [153-10-424-00-001000](#) [153-10-422-00-001000](#) [153-10-420-00-001000](#) [153-10-328-00-001000](#) [153-10-324-00-001000](#) [153-10-322-00-001000](#) [153-10-320-00-001000](#) [153-10-318-00-001000](#) [153-10-316-00-001000](#) [153-10-314-00-001000](#) [153-10-310-00-001000](#) [153-10-308-00-001000](#) [153-10-306-00-001000](#) [153-10-304-00-001000](#) [153-10-210-00-001000](#)

[150-90-964-00-001000](#) [150-90-952-00-001000](#) [150-90-950-00-001000](#) [150-90-652-00-001000](#) [150-90-650-00-001000](#) [150-90-648-00-001000](#) [150-90-642-00-001000](#) [150-90-640-00-001000](#) [150-90-636-00-001000](#) [150-90-632-00-001000](#) [150-90-628-00-001000](#) [150-90-624-00-001000](#) [150-90-432-00-001000](#) [150-90-428-00-001000](#) [150-90-424-00-001000](#) [150-90-422-00-001000](#) [150-90-420-00-001000](#) [150-90-328-00-001000](#) [150-90-324-00-001000](#) [150-90-322-00-001000](#) [150-90-320-00-001000](#) [150-90-318-00-001000](#) [150-90-316-00-001000](#) [150-90-314-00-001000](#) [150-90-310-00-001000](#) [150-90-308-00-001000](#) [150-90-306-00-001000](#) [150-90-304-00-001000](#) [150-90-210-00-001000](#)

[150-10-964-00-001000](#) [150-10-952-00-001000](#) [150-10-950-00-001000](#) [150-10-652-00-001000](#) [150-10-650-00-001000](#) [150-10-648-00-001000](#) [150-10-642-00-001000](#) [150-10-640-00-001000](#) [150-10-636-00-001000](#) [150-10-632-00-001000](#) [150-10-628-00-001000](#) [150-10-432-00-001000](#) [150-10-428-00-001000](#) [150-10-424-00-001000](#) [150-10-422-00-001000](#) [150-10-420-00-001000](#) [150-10-328-00-001000](#) [150-10-324-00-001000](#) [150-10-322-00-001000](#) [150-10-320-00-001000](#) [150-10-316-00-001000](#) [150-10-314-00-001000](#) [150-10-310-00-001000](#) [150-10-308-00-001000](#) [150-10-306-00-001000](#) [150-10-304-00-001000](#) [150-10-210-00-001000](#) [150-10-624-00-001000](#) [150-10-318-00-001000](#)

[150-40-964-00-001000](#) [150-40-952-00-001000](#) [150-40-950-00-001000](#) [150-40-652-00-001000](#) [150-40-650-00-001000](#) [150-40-648-00-001000](#) [150-40-642-00-001000](#) [150-40-640-00-001000](#) [150-40-636-00-001000](#) [150-40-632-00-001000](#) [150-40-628-00-001000](#) [150-40-432-00-001000](#) [150-40-428-00-001000](#)