LP2N 5.08/90





LP2H 5.08/90



LP2HR 5.08/90



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm²/AWG)	4.0	26…12	26…12

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 58

Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm²/AWG)	4.0	26…12	26…12

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 58

Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm²/AWG)	4.0	26…12	26…12

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 58

Solder pin length		4.5 mm	4.5 mm	
Color				
Poles	Type	Part No.	Part No.	Qty.
4	LP2N 5.08/4/90	**1635150000**	**1695900000**	50
6	LP2N 5.08/6/90	**1625550000**	**1695910000**	50
8	LP2N 5.08/8/90	**1596470000**	-	
10	LP2N 5.08/10/90	**1596500000**	-	
12	LP2N 5.08/12/90	**1632560000**	-	
14	LP2N 5.08/14/90	**1632570000**	-	
16	LP2N 5.08/16/90	**1596520000**	-	
18	LP2N 5.08/18/90	**1632580000**	-	
20	LP2N 5.08/20/90	**1596560000**	-	
22	LP2N 5.08/22/90	**1632590000**	-	
24	LP2N 5.08/24/90	**1596600000**	-	
26	LP2N 5.08/26/90	**1632600000**	-	
28	LP2N 5.08/28/90	**1632610000**	-	
30	LP2N 5.08/30/90	**1596640000**	-	
32	LP2N 5.08/32/90	**1632620000**	-	
34	LP2N 5.08/34/90	**1632630000**	-	
36	LP2N 5.08/36/90	**1632640000**	-	
38	LP2N 5.08/38/90	**1632650000**	-	
40	LP2N 5.08/40/90	**1632660000**	-	
42	LP2N 5.08/42/90	**1632670000**	-	
44	LP2N 5.08/44/90	**1632680000**	-	
46	LP2N 5.08/46/90	**1632690000**	-	
48	LP2N 5.08/48/90	**1632700000**	-	

Accessories	Page
Marking	40
Mounting	46
Miscellaneous	43, 45, 46

Solder pin length		4.5 mm	4.5 mm	
Color				
Poles	Type	Part No.	Part No.	Qty.
4	LP2H 5.08/4/90	**1668630000**	**1697320000**	50
6	LP2H 5.08/6/90	**1625590000**	**1697330000**	50
8	LP2H 5.08/8/90	**1596690000**	-	
10	LP2H 5.08/10/90	**1596710000**	-	
12	LP2H 5.08/12/90	**1632860000**	-	
14	LP2H 5.08/14/90	**1632870000**	-	
16	LP2H 5.08/16/90	**1596730000**	-	
18	LP2H 5.08/18/90	**1632880000**	-	
20	LP2H 5.08/20/90	**1596750000**	-	
22	LP2H 5.08/22/90	**1632890000**	-	
24	LP2H 5.08/24/90	**1596770000**	-	
26	LP2H 5.08/26/90	**1632900000**	-	
28	LP2H 5.08/28/90	**1632910000**	-	
30	LP2H 5.08/30/90	**1596790000**	-	
32	LP2H 5.08/32/90	**1632920000**	-	
34	LP2H 5.08/34/90	**1632930000**	-	
36	LP2H 5.08/36/90	**1632940000**	-	
38	LP2H 5.08/38/90	**1632950000**	-	
40	LP2H 5.08/40/90	**1632960000**	-	
42	LP2H 5.08/42/90	**1632970000**	-	
44	LP2H 5.08/44/90	**1632980000**	-	
46	LP2H 5.08/46/90	**1632990000**	-	
48	LP2H 5.08/48/90	**1633000000**	-	

Accessories	Page
Marking	40
Mounting	-
Miscellaneous	43, 45

Solder pin length		4.5 mm	4.5 mm	
Color				
Poles	Type	Part No.	Part No.	Qty.
4	LP2HR 5.08/4/90	**1636290000**	**1697340000**	50
6	LP2HR 5.08/6/90	**1636300000**	**1697350000**	50
8	LP2HR 5.08/8/90	**1636310000**	-	
10	LP2HR 5.08/10/90	**1636320000**	-	
12	LP2HR 5.08/12/90	**1668640000**	-	
14	LP2HR 5.08/14/90	**1668650000**	-	
16	LP2HR 5.08/16/90	**1636330000**	-	
18	LP2HR 5.08/18/90	**1668660000**	-	
20	LP2HR 5.08/20/90	**1636340000**	-	
22	LP2HR 5.08/22/90	**1668670000**	-	
24	LP2HR 5.08/24/90	**1636350000**	-	
26	LP2HR 5.08/26/90	**1668680000**	-	
28	LP2HR 5.08/28/90	**1668690000**	-	
30	LP2HR 5.08/30/90	**1636360000**	-	
32	LP2HR 5.08/32/90	**1668700000**	-	
34	LP2HR 5.08/34/90	**1668710000**	-	
36	LP2HR 5.08/36/90	**1668720000**	-	
38	LP2HR 5.08/38/90	**1668730000**	-	
40	LP2HR 5.08/40/90	**1668740000**	-	
42	LP2HR 5.08/42/90	**1668750000**	-	
44	LP2HR 5.08/44/90	**1668760000**	-	
46	LP2HR 5.08/46/90	**1668770000**	-	
48	LP2HR 5.08/48/90	**1668780000**	-	

Accessories	Page
Marking	40
Mounting	-
Miscellaneous	43, 45