



World Leader in Network and Electrical Solutions

Current refinements (click to remove)

[Region](#) ▶ [USA](#) [Product Family](#) ▶ [HSTTV Heat Shrink on 100 Ft. Reels](#) [Text Search: 'HSTTV150-C'](#)

Your search criteria matched only one product, shown below.



Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing on Small Reels

- For dry locations
- Highly flame retardant
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 3

Part Number:	HSTTV150-C
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink (UL224 VW-1)
Material:	Polyolefin cross-linked
Color:	Black
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/5 Class 3
UL Recognized:	E122770
Length (ft.):	100
Length (m):	30.5
Flammability Rating:	UL224 VW-1
Max. Recovered I.D. (In.):	.750
Max. Recovered I.D. (mm):	19.0
Min. Expanded I.D. (In.):	1.50
Min. Expanded I.D. (mm):	38.1
Nominal Diameter / Size:	1 1/2
Nominal Recovered Wall Thickness (In.):	.040
Nominal Recovered Wall Thickness (mm):	1.0
Shrink Ratio:	2:1
Temperature Range:	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.