

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130106-0120](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Haztex® Hazardous Location 26 Watt Fluorescent 5 Drops Stringlight 12/3 SOOW
19.81m Length 5 Lamps

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR39801

General

Product Family Portable Lighting
Series [130106](#)
NEMA Configuration NEMA 5-15
NEMA Rating Rain Tight
Outlet None
Overview [Stringlights](#)
Product Literature Order No 987650-8055
Product Name Haztex®
Type String Lights
UPC 78678834307
Woodhead Yes

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary N/A
Depth 100.08mm (3.940")
Duty Hazardous
Guard Included No
Guard Type N/A
Height 482.60mm (19.000")
Length 19.81m (65.0')
Material - Globe Tempered Glass
Material - Guard Cast Aluminum
Mounting Style Stringer
Packaging Type Carton
Socket Construction Rubber Molded

Electrical

Bulb Type Fluorescent
Cord Type - Primary 12/3 SOOW
Cord Type - Secondary 14/3 SOOW
Lamp Type PL-C 26/41/4P
Lamp Wattage - Maximum 26W
Lumens 1800
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 342510A



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130106Series](#)