



## Search Results

### Evaluate

- FAQ's
- Line Cards
- PDF-NetKey Cabli ..

### Design a Solution

- Part Drawings
- PDF-NetKey Fiber ..
- Specification Sheets
- PDF-NetKey Fiber ..

### How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 


 **Text Search: 'NKFLCSMWH'**

Your search criteria matched only one product, shown below

## NKFLCSMWH



- Meets TIA/EIA-568-B.3 requirements
- Insertion loss: .1dB typical (multimode), .2dB typical (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Field polish termination -- Panduit recommends anaerobic adhesive
- Use Field Polish Termination Kit (FIELDKIT)

• Part Number	NKFLCSMWH
• RoHS Compliancy Status	Compliant
• Part Description	NetKey® LC 62.5/125µm Multimode Simplex Connector, Electric Ivory (EI) body, White (WH) boot.
• Product Type	NetKey® Network Components
• Boot Color	White (WH)
• Pricing Description	Netkey LC 62.5/125µm Multimode Simplex Connector (EI Body WH Boot)
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.