


ORDERING CODE BC12AA

SOLDER LUGS = L
(6") WIRE LEADS = W
9 VOLT TYPE SNAPS =SF

DATE	SYM	REVISION RECORD	AUTH	DR.	CK.
5/06/06	C	ADDED CONTACT RESI. INFO.	T.B.	B.S.	
1/12/08	D	RANGE WAS "RANGEE"	T.B.	B.S.	
2/22/13	E	DIM. 16.00 WAS 16.20 DIM. 108.0 WAS 107.9 UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	



SPECIFICATIONS :

Plastic material - polypropylene
Flammability Rating-UL94 HB, UL File No. E216959
Temperature Range: -10°C to +100°C
Springs - nickel plated spring steel Wire - 152.4 mm Ref.Long 26 AWG,
UL1007, CSA - TR-64, 300V, 80° C.
Rivets - Brass, nickel plated
9 Volts Snaps - Brass, nickel plated
Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000
ROHS 2 COMPLIANT

Note: Dimensions in mm. (inches)

TOLERANCES (EXCEPT AS NOTED)		 Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735	
DECIMAL + - .5 (.020")		SCALE NONE	DRAWN BY S.C. APPROVED BY
FRACTIONAL + - .8 (.030")	TITLE TWO "AA" CELL HOLDER		
ANGULAR + 3° -	DATE 2/22/2013	DRAWING NUMBER BC12AAW	