


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	FIBER TYPE	JACKET RATING	DIAMETER	BEND RADIUS	
				INSTALLED	LONG TERM
FSPR91AY	SINGLEMODE 9/125UM	OFCR	31.1mm [1.224"]	64.2cm [25.3"]	32.1cm [12.7"]
FSP91AY		OFCP			
FSPL91AY		OFCR-LS			
FSPR51AY	MULTIMODE 50/125UM	OFCR	31.1mm [1.224"]		
FSP51AY		OFCP			
FSPL51AY		OFCR-LS			
FSPR61AY	MULTIMODE 62.5/125UM	OFCR	31.1mm [1.224"]		
FSP61AY		OFCP			
FSPL61AY		OFCR-LS			
FOPRX1AY	MULTIMODE 50/125UM OM3	OFCR	31.1mm [1.224"]		
FOPPX1AY		OFCP			
FOPLX1AY		OFCR-LS			
FOPRZ1AY	MULTIMODE 50/125UM OM4	OFCR	31.1mm [1.224"]		
FOPPZ1AY		OFCP			

										OPTI-CORE 144 FIBER ARMORED DISTRIBUTION CABLE WITH 12 SUB-UNITS OF 12 FIBERS CUSTOMER DRAWING
02	10-26-09	EFK		RELEASED TO PRODUCTION	02055-102					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	

	PANDUIT TM CORP. TINLEY PARK, ILL 60477
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± 0.3 (.010) (.XX) ± 0.8 (.03) ANGLES
DRAWN BY MC	REVIEW DRAWING NUMBERS
DATE 06-03-05	
CHK'D WMA	

DRAWING FILENAME M02055BX_DC_144/01A	SCALE NONE
PART NO. FSP**1AY FOP**1AY	DRAWING NO. 02055-102 SHEET 2 OF 2
SIZE A	