



För icke direkt toleranssatta mått gäller toleransklass General tolerances if not otherwise stated		Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
		1	1015830000	4 101-2145, 4 101-2120 ÄNDRAD/CHANGED	030325	SE
		2	1023850000	4 101-3779 W. 4 101-2053	050823	jowi

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2


Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.
Additional general tolerances in accordance with drawing 4100-4644.



KASSETT LASERMÄRKT ENLIGT RITNING 4101-2145
CASSETTE LASERMARKED ACCORDING TO DRAWING 4101-2145



Material		Behandling/Treatment			Status	
					Frisläppt	
Konstr/Design	Ritad/Drawn	Datum/Date	Skala/Scale	Kontroll/Checked	Godkänd/Approved	Anmärkning/Blank
JOWI	SE	2005-08-23	1:1	TGW	NE	
pressmaster®			Benämning/Denomination		Vikt/Veigt, gram	
ISO 9001 REG NR FM13687			V-blad kassett V-blade cassette		Art grp 012	
					REV	
					002	