


.025 ± .002 (1/16A-10A)
.032 ± .002 (12A-15A)



NOTES:

1. UL RECOGNIZED THRU 15A & CSA CERTIFIED.
INTERRUPTING CAPACITY TO 300A DC AT 125V,
50A AC AT 125V
2. MATERIALS:
BODY - GLASS
COATING - INSULATING EPOXY
LEADS - SOLDER COATED COPPER
3. TO BE STAMPED WITH L/F & AMPERAGE
ON 2 OPPOSITE SIDES.

DESCRIPTION

DE NOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
