



## Clean Cut

### Scissor Cut for Easy, Fray Resistant Installation in Production or Field

By adjusting the physical characteristics of the polyethylene terephthalate filaments, the engineers at Techflex have produced a product with the same specifications as our PET with the unique advantage of being able to cut the material with ordinary scissors and still maintain an extraordinarily fray-resistant end.

FLEXO CLEAN CUT (CC) is ideal for field installers and other situations where access to a hot knife is impossible. CC's fray-resistant properties allows frequent expansion at the cut end without unraveling. When cut with a hot knife, CC produces a virtually frayless end. Clean Cut sets the highest standard for uncoated fray resistance sleeving products.

- **Resists Fraying when Cut with Scissors**
- **Increased Braid Density for Fuller Coverage**
- **High Abrasion Resistance**
- **Temperature Range -94°F to 257°F**
- **Melt Temp. 482°F**



Clean Cut cuts easily and neatly with regular scissors and maintains a fray resistant end during installation.



When scissor cut, the end of Clean Cut will withstand heavier handling without fraying than standard PT.

| Nominal Size | Part #    | Expansion Range |         | Standard Spool Put-Ups |            | Available Colors | Lbs/100' |
|--------------|-----------|-----------------|---------|------------------------|------------|------------------|----------|
|              |           | Min.            | Max.    | Bulk Spool             | Shop Spool |                  |          |
| 1/8"         | CCP0.13   | 1/8"            | 1/4"    | 1,000'                 | 100'       | BK & GY          | 0.40     |
| 1/4"         | CCP0.25   | 5/32"           | 7/16"   | 1,000'                 | 100'       | BK & GY          | 0.46     |
| 3/8"         | CCP0.38   | 3/16"           | 5/8"    | 500'                   | 100'       | BK & GY          | 0.74     |
| 1/2"         | CCP0.50   | 1/4"            | 3/4"    | 500'                   | 100'       | BK & GY          | 0.82     |
| 3/4"         | CCP0.75   | 5/8"            | 1"      | 250'                   | 75'        | BK & GY          | 1.11     |
| 1"           | CCP1.00   | 3/4"            | 1 3/16" | 250'                   | 50'        | BK & GY          | 1.24     |
| 1 1/4"       | CCP1.25   | 1"              | 1 1/2"  | 250'                   | 50'        | BK & GY          | 1.56     |
| 1 1/2"       | CCP1.50   | 1 1/4"          | 2"      | 250'                   | 50'        | BK & GY          | 1.85     |
| 1 3/4"       | CCP1.75BK | 1 1/2"          | 2 1/8"  | 200'                   | 50'        | BK               | 2.30     |
| 2"           | CCP2.00BK | 1 3/4"          | 2 1/2"  | 200'                   | 50'        | BK               | 2.80     |

