




FEATURES:

- Permits single or double banana plug to be used with equipment having three circuit phone jacks.
- Tip connected to hot side of adapter and ring connected to ground side.
- Sleeve. No connection.
- Cross holes 4.2 (.166) dia. in plug body provide side stackup.

MATERIALS:

Upper Conn: Binding Posts

Material: Body & Collars; Brass, Comm'l, H.H. per QQ-B-626, Alloy 360.

Finish: Nickel plated per QQ-N-290, Class 2, .0002/.0003.

Insulation: Polycarbonate molded to collars.

Color: One red, one black.

Operating Temperature: +115° C. (+239° F.) Max.

Body Insulation: Acrylonitrile – Butadiene – Styrene, molded to Binding Posts and Phone Plug.

Color: Black.

Operating Temperature: +50° C. (+122° F.) Max.

Marking: "POMONA ELECTRONICS 2112."

Lower Conn: Phone Plug, PJ-051 per MIL-P-642.

RATINGS (Entire – Assembly):

Operating Temperature: +50° C. (+122° F.) Max.

Operating Voltage: 500 VRMS.

Current: 5 Amperes Cont.

ORDERING INFORMATION: Model 2112

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA