

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1301050043**
Status: **Active**
Overview: Specialty Lighting
Description: Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer Cast Aluminum Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series 130105
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 4X
 Outlet None
 Overview Specialty Lighting
 Product Name Watertite
 Type Hand Lamps, Specialty Light
 UPC 78678862503

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary 7.62m (25.0')
 Depth 120.65mm (4.750")
 Duty Wet Location
 Guard Included Yes
 Guard Type Cast Aluminum
 Height 457.20mm (18.000")
 Length N/A
 Material - Globe Tempered Glass
 Material - Guard Cast Aluminum
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SOOW
 Cord Type - Secondary 14/2 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ
 Voltage (Secondary) - Maximum 12V AC

Material Info

Engineering Number 1631-12A



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

130105 Series