

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190950024](#)
Status: **Active**
Description: Terminal Lugs for 22-18 AWG, Insulated Red Sleeve, Stud Size 6 (M3.5), Length 28.17mm (1.109")

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Ring and Spade Terminals
Series	19095
Comments	Type II Insulated; Class 1 and 2
Crimp Quality Equipment	Yes
Mil-Spec	AS17143-4, MS17143-4
Product Name	Avikrimp™
Type	Ring

Physical

Barrel Type	Closed
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	2.540µm (100µ")
Plating min - Termination	2.540µm (100µ")
Stud Size	6 (M3.5)
Wire Size AWG	18, 20, 22

Material Info

Old Part Number	AA-881-1
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19095-006

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19095Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19095-0024](#)