


DURATOOL

- 
- High quality ball bearing steel
 - 63 - 65 Rockwell Hardness (HRC)
 - 2-Component ESD Ergonomic handles, soft comfortable gripping surface, hard plastic core
 - Dual leaf springs in blue steel
 - Matched bearing rings to minimize metal-metal contact and friction
- Lap joint with screw to achieve a high level of strength and precision
 - Static dissipative ($10^6 - 10^8 \Omega/\text{sq.}$), oil, grease and wear-resistant

531558

Mftrs. List No.	Jaw	Overall length inch mm	Order Code	+	Price Each +	+
Long Snipe Nose						
D01013	Smooth	5.6"	143	169-6527	— —	— —
D01014	Serrated	5.6"	143	169-6528	— —	— —
Snipe Nose						
D01015	Smooth	5.2"	133	169-6529	— —	— —
D01016	Serrated	5.2"	133	169-6530	— —	— —
Flat Nose						
D01017	Smooth	5.2"	133	169-6532	— —	— —
Round Nose						
D01018	Smooth	5.2"	133	169-6533	— —	— —