

FLK 16/EZ-DR/ 100/KONFEK

Order No.: 2299301

The illustration shows a 20-position version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2299301>

Round cable set, with two 16-pos. socket strips (1:1 connection), cable length: 1 m

Commercial data

GTIN (EAN)	 4 017918 886035
sales group	I680
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 264 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
03/22/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m
Ambient temperature (operation)	-20 °C ... 50 °C

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	16
Number of positions, control side	16
Number of connectors, control side	1
Number of positions, module side	16
Number of connectors, modul side	1
Fixed cable length	1 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	6.5 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Certificates / Approvals



Certification	GOST
Certifications applied for:	UL / CUL

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;