


Type	Size	Description	Part No.
Incandescent	G11 (G-3½)	Miniature Screw lamp (MES)	(see table)



Drawing not to scale
All dimensions in mm

PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
328285	G638	1.25V 0.3W	1.25	225	250	275	0.75	1.0	1.25	S-2	10
328297	G627	2.5V 0.5W	2.5	180	200	220	3.0	3.8	4.5	C-2R	10
526952	G628	2.5V 0.63W	2.5	225	250	275	5.0	5.6	6.0	C-2R	30
265305	G191	3.5V 0.52W	3.5	135	150	165	1.0	1.5	2.0	C-2R	5000
328303	G647	3.5V 1.05W	3.5	270	300	330	4.5	6.0	7.5	C-2R	1000
526964	G978	3.8V 0.84W	3.8	207	220	233	7.6	9.0	10.3	C-2R	25
328315	G991	6V 0.24W	6.0	36	40	44	0.35	0.45	0.55	C-2R	10000
328327	G198	6V 0.36W	6.0	54	60	66	0.75	1.0	1.25	C-2R	10000
328339	G473	6.5V 0.98W	6.5	135	150	165	4.8	6.0	7.2	C-2R	3000
328340	G501	6.5V 1.95W	6.5	270	300	330	10	12	14	C-2R	4000
328352	G573	12V 1.2W	12	90	100	110	3.7	5	6.3	C-2V	5000
328364	G987	12V 2.2W	12	165	183	201	8.5	11	13.5	C-2V	3000
328376	G592	24V 1.2W	24	45	50	55	3.0	4.0	5.0	C-2F	5000
328388	G650	24V 2.8W	24	102	116	130	9.0	12.0	15.0	C-2F	3000

NOTES:

- 1) E10/13 nickel-plated screw cap in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-22-x.
- 2) Metal base to be durably marked with rating and trademark.