

CATALOG LISTING
LSQYUB3KC319
SHEET: 1 OF 1


ISSUE
1

REVISIONS




FORMTEK
DRAWN

RELEASE NO. PR-24408
REPLACES

CHECK
29 FEB 00
SAV
CHECK
29 FEB 00
GRT



CORROSION RESISTANT
STEEL SHAFT WITH
STRAIGHT KNURL



ON THIS DIAGRAM REFER TO
CONNECTOR PINS ONLY VIEWED
FROM END OF CONNECTOR

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING TORQUE----- 4 IN LBS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
FULL TRAVEL TORQUE ----- 4 IN LBS MAX		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
TOTAL TRAVEL----- 75° REF		ONE PLACE (.0) ±.030
PRETRAVEL ----- 5° MAX		TWO PLACE (.00) ±.015
DIFFERENTIAL TRAVEL----- 5° MAX		THREE PLACE (.000) ±.005
OVERTRAVEL ----- 70° MIN		ANGLES ±
		WEIGHT

- NOTES
- 1 - SWITCH USES FLUOROSILICONE SEALS IN OPERATING HEADS ONLY
 - 2 - SWITCH CAVITY EPOXY FILLED

ANSI Y14.5M-1982 APPLIES