

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1300240184](#)  
**Status:** **Active**  
**Overview:** [Brad Mini-Change Connectors](#)  
**Description:** Mini-Change Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 22 AWG.  
DeviceNet Thin (Drop) Cable, 0.305m (1.0') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E152210

**General**

Product Family Industrial Cordsets  
Series [130024](#)  
Connector End A Mini-Change  
Connector End B Pigtail  
IP Rating IP67  
Material - Contact Brass  
Overview [Brad Mini-Change Connectors](#)  
Product Name DeviceNet Trunk, Mini-Change  
Region Europe  
Type Single Ended  
UPC 78678822200

**Physical**

Cable Diameter 8.38mm (.330")  
Cable Length 0.305m (1.0')  
Color - Cable Jacket Gray  
Coupling Style Threaded  
Gender Male-Pigtail  
Keyway Single  
LED Indicator No  
Material - Cable Jacket PVC  
Material - Connector Body PVC  
Material - Coupling Nut Die-Cast Zinc  
Material - Plating Mating Gold  
Orientation Straight to Pigtail  
Poles 5  
Temperature Range - Operating -20°C to +80°C  
Wire Size AWG 22  
Wire/Cable Type Thin (Drop)

**Electrical**


Current - Maximum per Contact 4.0A  
Voltage - Maximum 300V AC/DC

**Material Info**

Engineering Number DND01A-0010

**Reference - Drawing Numbers**

Sales Drawing SD-130024-090



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130024](#) Series