



LOC	DIST	P	F	ZONE	LTR	REVISIONS	DATE	APPRO
6	14					REV, RDRW, & SM PKG PER 0720-0040-93	4-8-93	18 DAP



AMP WIRE RANGE		E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
22-16 AWG		MILITARY P/N AND CLASS	
SOLID OR STRANDED		NOT APPLICABLE	

STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
SOLID OR STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES ±

FINISH
TIN PLATE
0.00254 [1.000100] MIN
THK PER MIL-T-10727

DR 4-8-93
TA BRINKMAN
CHK 4-8-93
DA PATTERSON
APPD 4-8-93
DE MILLER
APPD 4-8-93
JL MECKLEY
PRODUCT SPEC

NAME	AMP	AMP Incorporated Harrisburg, PA 17105-3508
QUANTITY	100	LOOSE PIECE, BOX
PACKAGE TYPE	8-321288-1	LOOSE PIECE
PART NO	321288	