





2				1				
LOC	DIST	REVISIONS						
DW	—	P	LTR	DESCRIPTION		DATE	DWN	APVD
			E	REVISED (ECR-13-000755)		18JAN13	JL	WK



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6MM)
(TOP VIEW) (TOLERANCE: ±0.05)



OBSOLETE 4	BLUE	38.4	35.00 ±0.20	40.0	15	3-1470224-5
		35.9	32.50 ±0.20	37.5	14	3-1470224-4
		33.4	30.00 ±0.20	35.0	13	3-1470224-3
		30.9	27.50 ±0.20	32.5	12	3-1470224-2
		28.4	25.00 ±0.20	30.0	11	3-1470224-1
		25.9	22.50 ±0.15	27.5	10	3-1470224-0
		23.4	20.00 ±0.15	25.0	9	2-1470224-9
		20.9	17.50 ±0.15	22.5	8	2-1470224-8
		18.4	15.00 ±0.15	20.0	7	2-1470224-7
		15.9	12.50 ±0.10	17.5	6	2-1470224-6
		13.4	10.00 ±0.10	15.0	5	2-1470224-5
		10.9	7.50 ±0.10	12.5	4	2-1470224-4
		8.4	5.00 ±0.10	10.0	3	2-1470224-3
		5.9	2.50 ±0.10	7.5	2	2-1470224-2
	IVORY	38.4	35.00 ±0.20	40.0	15	1-1470224-5
		35.9	32.50 ±0.20	37.5	14	1-1470224-4
		33.4	30.00 ±0.20	35.0	13	1-1470224-3
		30.9	27.50 ±0.20	32.5	12	1-1470224-2
		28.4	25.00 ±0.20	30.0	11	1-1470224-1
		25.9	22.50 ±0.15	27.5	10	1-1470224-0
		23.4	20.00 ±0.15	25.0	9	0-1470224-9
		20.9	17.50 ±0.15	22.5	8	0-1470224-8
		18.4	15.00 ±0.15	20.0	7	0-1470224-7
		15.9	12.50 ±0.10	17.5	6	0-1470224-6
		13.4	10.00 ±0.10	15.0	5	0-1470224-5
		10.9	7.50 ±0.10	12.5	4	0-1470224-4
		8.4	5.00 ±0.10	10.0	3	0-1470224-3
		5.9	2.50 ±0.10	7.5	2	0-1470224-2
HSG. COLOR		C	B	A	POS.	PART NUMBER

- NOTE:
- MATERIAL:
HOUSING: PA66, UL 94V-2, COLOR: SEE TABLE.
CONTACTS: BRASS.
 - FINISH:
CONTACTS: 1.27µm [50µ"] MIN. BRIGHT-TIN ON SOLDER TAIL, WITH ENTIREC CONTACT UNDERPLATED 0.381µm [15µ"] MIN. NICKEL.
 - WAVE SOLDER CAPABLE TO 240°C PER TE CONNECTIVITY TEST SPEC. 109-202, CONDITION A.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 19DEC2006	TE Connectivity			
		CHK S. HOU 19DEC2006				
		APVD W.J. KE 19DEC2006	NAME			
DIMENSIONS: MM		PRODUCT SPEC 108-57175	2.5mm PITCH EMIX POST HEADER, VERTICAL TYP			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		QUALIFICATION TEST REPORT 501-57195				
MATERIAL SEE NOTE		FINISH SEE NOTE	SIZE A3	CAGE CODE 00779	DRAWING NO C=1470224	RESTRICTED TO —
		WEIGHT —	CUSTOMER DRAWING		SCALE —	SHEET 1 OF 2
					REV E	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

POLY BAG


CARTON

340mm(L)X470mm(W)X158mm(H)

(FOR P/N 0-1470224-2~0-1470224-5)

340mm(L)X470mm(W)X316mm(H)

(FOR P/N 0-1470224-6~1-1470224-5)



OBSOLETE			
12,960	180	3-1470224-5	1-1470224-5
12,000	200	3-1470224-4	1-1470224-4
14,400	200	3-1470224-3	1-1470224-3
16,000	250	3-1470224-2	1-1470224-2
16,000	250	3-1470224-1	1-1470224-1
20,000	250	3-1470224-0	1-1470224-0
21,600	300	2-1470224-9	0-1470224-9
25,200	350	2-1470224-8	0-1470224-8
28,000	350	2-1470224-7	0-1470224-7
35,000	350	2-1470224-6	0-1470224-6
20,000	500	2-1470224-5	0-1470224-5
24,000	600	2-1470224-4	0-1470224-4
30,000	750	2-1470224-3	0-1470224-3
36,000	1000	2-1470224-2	0-1470224-2
APQ (PCS/CARTON)		PPQ (PCS/BAG)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN O. HU 19DEC2006

CHK S. HOU 19DEC2006

APVD W.J. KE 19DEC2006

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

2.5mm PITCH EMIX POST HEADER,
VERTICAL TYP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1470224

SCALE

SHEET

2 OF 2

REV E