



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D	REVISED PER ECO-14-011808	09AUG2014	AP	SB

D




C

B



- CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- MATERIAL:
MOLDED PARTS - GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED.
COLOR: BLACK
SHELLS - STEEL PER ASTM A109.
- FINISH:
SHELL - .000200 MIN TIN PLATE OVER .000100 MIN COPPER UNDERPLATE.
- FINISH:
SHELL - ZINC PLATED .000200-.000400 THICK, YELLOW CHROMATE COATING.

STANDARD	4	.120	1658640-2
STANDARD	3	.120	1658640-1
PACKAGING TYPE	FINISH	DIM A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. REITZEL 29 JUL 03	 TE Connectivity						
DIMENSIONS: INCHES			CHK S. BOLASH 29 JUL 03							
			APVD M. WALMSLEY 29 JUL 03	NAME RECEPTACLE CONNECTOR, SIZE 5, 50 POS., AMPLIMITE HDP —						
			PRODUCT SPEC 108-40005							
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPLICATION SPEC 114-40030							
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ± 2'			SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL			WEIGHT —				A2	00779	C-1658640	—
			SEE TABLE			CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV D