



Hex 3/16" Female Screw Lock (Screw Lock Only - Style 1 & 2)



Style 1 & 2



G06B >>

Lyn-Tron Part ID: **SS9412-01**

Qty in Stock: **48,949**

Alternative Part Possibilities

Lyn-Tron Part ID	Qty In Stock
SS9412-00	0

This color represents the identical unplated part.

Conformity

Conforming:	RoHS WEEE REACH DFARS
Non Conforming:	N/A
Download Conformity Stmt	

Other Available Options

View	Material Specs
View	Finish App Summary
View	General Notes
Download	CAD Drawing
View CAD files with: Autodesk Brava	

Code	Description	Basic Part Number	A (Overall Length)	B (Head Length)	C (Thread Length)	Style	Female Thread	Male Thread
BR	Brass (RoHS Compliant)	9390	0.720	0.210	0.510	1.000	0440	0440
SS	Stainless Steel (RoHS Compliant)	9410	0.375	0.187	0.187	1.000	0440	0440
ST	Steel (RoHS Compliant)	9411	0.437	0.187	0.250	2.000	0440	0440
		9412	0.500	0.187	0.312	1.000	0440	0440
		9413	0.562	0.187	0.375	1.000	0440	0440
		9414	0.625	0.187	0.437	1.000	0440	0440
		9415	0.688	0.187	0.500	1.000	0440	0440
		9416	0.750	0.187	0.562	1.000	0440	0440

Code	Plate Description pertaining to material SS
00	Unplated
00D	Unplated - 202 Thread Lock Dri Loc IFI 125 / 525
00F	Nylon Strip (Fill)
00H	Heat Treat - Unplated
00P	Nylon Patch - Unplated
00Q	Nylon Pellet - Unplated
00S	Marking Stamp - Unplated
01	Passivate ASTM-A967-05
011	Passivate (Nitric) ASTM-A967-05
012	Passivate with 96 Hour Salt Spray ASTM-B-117 2 hour salt spray
01D	Passivate - #202 Thread Lock Dri Loc IFI 125 / 525
01E	Passivate with Electro Polish ASTM-A967-05
01H	Passivate + Heat Treat ASTM-A967-05