


Front panel interface

- IP65
- contains cover, frame, seals, fixings and designation tags


FrontCom® GH Key

lockable



FrontCom® GH Knob

lockable



Technical data

Version
Material
UL 94 flammability class
Colour
Resistance to shocks
Threaded bolts / screws
Durability
Ingress Protection Class
Pollution severity
Storage temperature

lockable housing
PPE
V-0
RAL 7004
2 years to DIN EN 50102
M5 / V2A
UV; Fuel; Oil
IP65 according to DIN EN 50102
3
-20 °C...+80 °C

Lockable housing
PPE
V-0
RAL 7004
2 years to DIN EN 50102
M5 / V2A
UV; Fuel; Oil
IP65 according to DIN EN 50102
3
-20 °C...+80 °C

Length x width x height

mm

33 x 101 x 136

33 x 101 x 136

Note

with 2 keys

with lock

Ordering data

Type	Qty.	Order No.
FRONTCOM GH KEY	1	1879200000




Type	Qty.	Order No.
FRONTCOM GH KNOB	1	1879210000

Note

Designation tags ESG8/17 1720610000
Felt pen STI-S 0508401694

Designation tags ESG8/17 1720610000
Felt pen STI-S 0508401694

Application



Front panel interface

Front panel interface

- IP65




FrontCom® AR Data

RJ45, USB, SUB D 9+25 pole



FrontCom® AR Plug

Adapter for 230 V earthed plug



Technical data

Version

Material
UL 94 flammability class
Colour
Storage temperature
Interfaces

Combination of 4 integral data interfaces,
wired 1:1
PPE
V-0
RAL 7004
-20 °C...+80 °C
USB: type A, socket-socket,
lockable when memory stick plugged in
RJ45: socket-socket, Cat.5 up to 100 MHz
SUB-D 9-pole: socket-plug
SUB-D 25-pole: socket-plug

Frame as receptacle for earthed power socket

Stainless steel

Length x width x height

mm

Note

85 x 101 x 136

59 x 101 x 136

Ordering data

Type	Qty.	Order No.
FRONTCOM AR DATA	1	1879220000



Type	Qty.	Order No.
FRONTCOM AR PLUG	1	1879230000

Note

Designation tags ESG8/17 1720610000
Felt pen STI-S 0508401694

Earthed power socket 8734580000

Application



Front panel interface

- IP65

FrontCom® AR

Universal



Technical data

[illegible]

Length x width x height	mm	2.5 x 101 x 136
-------------------------	----	-----------------

Note

Ordering data

[illegible]

Note

Application

